Enhancement Mode Gallium Nitride (GaN) HEMT

700 V, 75 mΩ, 21 A, PTFP-N9 (DFN)

NTMT100N70GN1


$V_{(BR)DSS}$	$R_{DS(ON)}$ TYP	I_{DS} MAX
700 V	75 mΩ	21 A


Features

- Low $R_{DS(ON)}$ to Minimize Conduction Losses
- Ultra Low Gate Charge for High Speed Switching
- FOM-Q_G = 280 nC*mΩ
- Small Footprint for High Density PCB Design
- This Device is Pb-Free, Halide Free and is RoHS Compliant

Typical Applications

- High Density Power Modules
- High Frequency AC-DC and DC-DC Converters
- High Performance PSU for Consumer and Industrial
- Resonant Conversion





PTFP-N9 8.00x8.00x0.90, 2.00P
(DFN)
CASE 522AG

MAXIMUM RATINGS (T_J = 25 °C unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	V_{DSS}	700	V
Drain-to-Source Transient Voltage, t_P < 200 μs	$V_{DS(TRAN)}$	800	V
Pulsed Drain-to-Source Voltage, T_J = 25 °C (t_{TOTAL} < 10 h) / T_J = 125 °C (t_{TOTAL} < 1 h)	$V_{DS(PULSE)}$	750	
Gate-to-Source Voltage	V_{GS}	−6 to 7	V
Gate-to-Source Transient Voltage, t_P = 50 ns, f_P = 100 kHz, Open Drain	$V_{GS(PULSE)}$	−20 to 10	V
Continuous Drain Current, T_{CASE} = 25 °C	I_{DS}	21	A
Pulsed Drain Current, t_P < 10 μs, T_C = 25 °C T_C = 125 °C	$I_{DS(PULSE)}$	41 23	A
Power Dissipation, V_{GS} = 6 V, T_{CASE} = 25 °C	P_{TOT}	111	W
Operating Junction Temperature	T_J	−55 to 150	°C
Storage Temperature	T_{STG}	−55 to 150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

MARKING DIAGRAM



MT100N70GN1	= Specific Device Code
A	= Assembly Location
YY	= Year
WW	= Work Week
ZZ	= Assembly Lot Code

ORDERING INFORMATION

Device	Package	Shipping†
NTMT100N70GN1TXG	PTFP-N9 (DFN)	2500 / Tape & Reel

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2026

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Junction-to-Case	$R_{\theta JC}$	1.12	°C/W
Junction-to-Ambient (Note 1)	$R_{\theta JA}$	66.4	°C/W
Maximum Soldering Temperature (MSL3)	T_{SLD}	260	°C

1. Device on 1 in^2, 2 oz copper pad on single layer FR-4 PCB.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V	700			V
Drain-to-Source Leakage Current	I_{DSS}	V_{GS} = 0 V, V_{DS} = 700 V		0.8	48	μA
		V_{GS} = 0 V, V_{DS} = 700 V, T_J = 125 °C		9		
Gate-to-Source Leakage Current	I_{GSS}	V_{GS} = 6 V, V_{DS} = 0 V		45		μA
ON CHARACTERISTICS						
Drain-to-Source On Resistance	$R_{DS(ON)}$	V_{GS} = 6 V, I_{DS} = 0.5 A		75	100	mΩ
		V_{GS} = 6 V, I_{DS} = 6 A		75		
		V_{GS} = 6 V, I_{DS} = 6 A, T_J = 125 °C		151		
Gate Threshold Voltage	$V_{GS(TH)}$	V_{DS} = V_{GS}, I_{DS} = 19.5 mA, T_J = 25 °C	1.2	1.6	2.5	V
		V_{DS} = V_{GS}, I_{DS} = 19.5 mA, T_J = 125 °C		1.5		
DYNAMIC CHARACTERISTICS						
Input Capacitance	C_{ISS}	V_{DS} = 400 V, V_{GS} = 0 V, f = 100 kHz		139		pF
Output Capacitance	C_{OSS}			47		
Reverse Transfer Capacitance	C_{RSS}			0.52		
Output Capacitance, Energy Related	$C_{OSS(ER)}$	V_{DS} = 0 V to 400 V, V_{GS} = 0 V		68.7		pF
Output Capacitance, Time Related	$C_{OSS(TR)}$			90.9		
Output Charge	Q_{OSS}			36.3		nC
Output Capacitance Stored Energy	E_{OSS}			5.5		μJ
Gate Resistance	R_G	f = 5 MHz		7		Ω
Gate Charge	Q_G	V_{DS} = 400 V, I_{DS} = 6 A, V_{GS} = 0/6 V		3.8		nC
Gate-to-Source Charge	Q_{GS}			0.3		
Gate-to-Drain Charge	Q_{GD}			1.4		
Gate Plateau Voltage	V_{PLAT}			2.1		V
REVERSE CONDUCTION CHARACTERISTICS						
Source-to-Drain Reverse Voltage	V_{SD}	V_{GS} = 0 V, I_{SD} = 6 A		2.4		V
Pulsed Reverse Current	$I_{SD(PULSE)}$	V_{GS} = 6 V, t_{PULSE} = 10 μs			41	A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (T_J = 25 °C unless otherwise noted)




Figure 1. Output Characteristics at T_J = 25 °C




Figure 2. Output Characteristics at T_J = 125 °C




Figure 3. On-Resistance vs. Drain Current at T_J = 25 °C




Figure 4. On-Resistance vs. Drain Current at T_J = 125 °C




Figure 5. Transfer Characteristics at V_{DS} = 3 V




Figure 6. Normalized On-Resistance vs. Temperature at V_{GS} = 6 V

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified) (continued)




Figure 7. Reverse Conduction Characteristics at T_J = 25 °C




Figure 8. Reverse Conduction Characteristics at T_J = 125 °C




Figure 9. Normalized Threshold Voltage vs. Temperature




Figure 10. Gate Charge Characteristics at I_{DS} = 20 A




Figure 11. Capacitance Characteristics




Figure 12. Drain Leakage Characteristics

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified) (continued)




Figure 13. Gate Leakage Characteristics




Figure 14. Transient Thermal Impedance




Figure 15. Safe Operating Area at T_C = 25 °C




Figure 16. Safe Operating Area at T_C = 125 °C

Share Feedback
Your Opinion Matters


Downloaded from Arrow.com.

REVISION HISTORY

Revision	Description of Changes	Date
0	Initial production document release.	6/17/2026


Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.




PTFP−N9 8.00x8.00x0.90, 2.00P
CASE 522AG
ISSUE O


DATE 04 MAY 2026




TOP VIEW



BOTTOM VIEW



SIDE VIEW



RECOMMENDED MOUNTING FOOTPRINT

*For additional information on Pb−Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NOTES:
1. ALL DIMENSION AND TOLERANCE CONFORM TO ASME Y14.5−2018.
2. ALL DIMENSION ARE IN MILLIMETERS
3. DRAWING NOT TO SCALE.
4. DIMENSION DO NOT INCLUDE MOLD PROTRUSION.
5. PACKAGE OUTLINE EXCLUSIVE OF METAL BURR DIMENSIONS.

MILLIMETER			
SYMBOL	MIN.	NOM.	MAX.
A	0.80	0.90	1.00
A1	0.00	0.02	0.05
A3		0.203 REF.	
b	0.95	1.00	1.05
D		8.00 BSC	
D2	6.84	6.94	7.04
E		8.00 BSC	
E2	3.10	3.20	3.30
e		2.00 BSC	
k1		1.00 REF.	
k2		2.80 REF.	
L	0.40	0.50	0.60
TOLERANCE FORM & POSITION			
aaa		0.10	
bbb		0.10	
ccc		0.10	
ddd		0.05	
eee		0.10	
fff		0.10	

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.


© Semiconductor Components Industries, LLC, 2026

Downloaded from Arrow.com.

PTFP−N9 8.00x8.00x0.90, 2.00P
CASE 522AG
ISSUE O

DATE 04 MAY 2026

GENERIC MARKING DIAGRAM*



XXXX = Specific Device Code
A = Assembly Location
YY = Year
WW = Work Week
ZZ = Assembly Lot Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2026

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.