

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting



1436550

<https://www.phoenixcontact.com/us/products/1436550>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, 4-position, Socket, angled, M12-SPEEDCON, D-coding, THR and wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1436550
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEHI
GTIN	4046356438612
Weight per piece (including packing)	13.643 g
Weight per piece (excluding packing)	10.265 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting



1436550

<https://www.phoenixcontact.com/us/products/1436550>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.2 Connectors for Outside Environment (Balanced cabling)
Order information:	Lock nut is included in the scope of delivery

Mounting

Mounting type	Front mounting (M12 x 1)
---------------	--------------------------

Product properties

Product type	Circular connectors (device side)
Application	Data
	Signal
Number of positions	4
Shielded	no
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	THR and wave soldering
Contact connection type	Socket

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting



1436550

<https://www.phoenixcontact.com/us/products/1436550>

Connector

Connection 1

Head design	Socket
Head cable outlet	angled
Head thread type	M12
Head locking type	SPEEDCON
Coding	D

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting




1436550

<https://www.phoenixcontact.com/us/products/1436550>

Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting



1436550
<https://www.phoenixcontact.com/us/products/1436550>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1436550>

	UL Recognized Approval ID: E118976-20100522			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	250 V	4 A	22	-

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting



1436550
<https://www.phoenixcontact.com/us/products/1436550>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-FSD-4CON-L90 SCO - Device connector front mounting



1436550

<https://www.phoenixcontact.com/us/products/1436550>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3abd4122-af42-494e-a2a8-9f8ecfa9c58e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com