



CONN 1
FEMALE STR
CODE Z WATER BLUE
WITHOUT CLIP SLOT
UNSEALED

TE P/N	L(mm)	REV
2081377-1	300+10/-0	A
2081377-2	600+10/-0	A
2081377-3	1000+15/-0	A
2081377-4	2000+20/-0	A
2081377-5	3000+30/-0	A
2081377-6	5000+40/-0	A

CONN 2
MALE STR
CODE Z WATER BLUE
WITHOUT CLIP SLOT
UNSEALED

NOTES:

1. ALL RF CONNECTORS MUST BE ASSEMBLED PER MANUFACTURER'S APPLICATION SPECIFICATIONS WITH FOLLOWING [SC]:
1.1: SOCKET CONTACTS CRIMP HEIGHT
1.2: FERRULES' CRIMP HEIGHT
1.3: CONNECTORS TO COAX CABLE RETENTION FORCE
2. 100% IN-PROCESS ELECTRICAL TEST:
2.1: DC CONTINUITY, FOR CENTER AND OUTER CONDUCTORS, POINT TO POINT
2.2: SHORT CIRCUITS;
3. TEMPERATURE RANGE: -40°C TO 85°C

4. LABEL CONTENT:

TE P/N: XXXXXXXX-X REV: X
DATE: YYYYMMDD

-X: FOLLOW DRAWING REVISION
-X: -1 OR -2 OR-3
DESCRIPTION:
YYYY: YEAR (EXAMPLE: 2016) MM:
MONTH (EXAMPLE: 02)
DD: DATE (EXAMPLE: 25)

AR	MM	TEAR TAPE FOR PACKAGING	12
1	PC	ID LABEL	11
AR	MM	RG174LL COAXIAL CABLE	10
1	PC	SUBASSY MALE	9
1	PC	CENTER CONTACT MALE	8
1	PC	RETAINER	7
1	PC	FAKRA MALE HSG 1P CADE Z	6
2	PC	OUTER FERRULE	5
1	PC	SUBASSY FEMALE	4
1	PC	CENTER CONTACT FEMALE	3
1	PC	RETAINER	2
1	PC	FAKRA HSG FEMALE 1P CODE Z	1
-X	U/M	DESCRIPTION	ITEM
QTY			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	Z.Z.ZHONG	23FEB2023
CHK	ERIC.DAI	23FEB2023
APVD	WENKE.HE	23FEB2023

DIMENSIONS:
mm

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

MATERIAL
-

FINISH
-

WEIGHT	-
--------	---

SIZE	A2
CAGE CODE	00779
DRAWING NO	C-2081377

CUSTOMER DRAWING	SCALE	-	SHEET	1 OF 1	REV	A
------------------	-------	---	-------	--------	-----	---

TE Connectivity

NAME
-

FAKRA STR FEMALE TO FAKRA STR MALE
WITHOUT CLIP SLOT RG174LL CODE Z