Specifications



Photo is representative

Eaton 187123

Eaton Moeller® series M30 Illuminated selector switch actuator, RMQ-Titan, With thumb-grip, maintained, 2 positions (V position), Blue, Metal bezel

General specifications

PRODUCT NAME	Eaton Moeller® series M30 illuminated selector switch
CATALOG NUMBER	187123
MODEL CODE	M30C-FWLKV-B
EAN	4015081821723
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	47 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.042 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660 CSA file No. 012528 CSA Class No.: 3211-03 DNV UL File No.: E29184 GL IEC/EN 60947-5 UL 508 CSA-C22.2 No. 14-05 CSA-C22.2 No. 94-91 CE marking UL Category Control No.: NKCR UL Listed CSA certified
GLOBAL CATALOG	187123
PRODUCT TYPE	Illuminated selector switch

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Illuminated selector switch actuator
ACTUATOR COLOR	Blue
ACTUATOR FUNCTION	Maintained Spring-return
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.

Resources

CATALOGS	eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf
DECLARATIONS OF CONFORMITY	eaton-illuminated-pushbutton-declaration-of-conformity-eu251546en.pdf
DRAWINGS	eaton-operating-m30-dimensions-004.eps eaton-operating-m30-dimensions-003.eps eaton-operating-m30-dimensions-006.eps eaton-operating-m30-dimensions-005.eps eaton-operating-symbol-002.eps eaton-general-m22-symbol.eps eaton-operating-3d-drawing-009.eps eaton-general-approval-m22-symbol.eps
ECAD MODEL	ETN.187123.edz
INSTALLATION INSTRUCTIONS	eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf
MCAD MODEL	eaton-switches-mcad-drawings-wahltaste-knebel-v-stellung.dwg DA-CS-wahltaste_knebel_v_stellung_flatfront

Downloaded from Arrow.com.

10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	2000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATOR TYPE	Toggle
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPENING DIAMETER	30 mm
OPERATING TORQUE	0.3 Nm
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON-	0 W

Downloaded from Arrow.com.

CURRENT-DEPENDENT PVS	
SWITCHING ANGLE	60 °
BEZEL COLOR	Titanium
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
BEZEL MATERIAL	Metal
DESIGN	With thumb-grip Flat front
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	NEMA 4X, 13
DEGREE OF PROTECTION (FRONT SIDE)	IP66
FUNCTIONS	Stay-put/spring-return function, can be changed with coding parts M22-XC-Y
INDICATOR COLOR	Blue
LENS TYPE	Round
LIFESPAN, MECHANICAL	100,000 Operations
NUMBER OF SWITCH POSITIONS	2
SIZE	Front dimensions: Ø 36 mm
PRODUCT CATEGORY	RMQ-Titan
SUITABLE FOR	Illumination

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Powering Business Worldwide

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.