



Part Number : [330122022](#)
Product Description : MX150 Female Terminal for Unsealed Connectors, Tin Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.
Series Number : 33012
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings
[330122022_sd.pdf](#)
[313025040-000.pdf](#)

Specifications
[AS-33012-002-001.pdf](#)
[AS-33012-002-CH-001.pdf](#)
[330120000-AS-KR-000.pdf](#)
[PS-33012-002-001.pdf](#)
[TS-33012-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	33012
Description	MX150 Female Terminal for Unsealed Connectors, Tin Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Comments	Right Reel Payoff, Large Polarization Rib; For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers; Not to be used with MX150 Sealed Connectors
Product Name	MX150
UPC	822350084260

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Gender	Female
Grip Code	18
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.434/g

Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.54mm max.
Wire Size (AWG)	18, 20
Wire Size mm ²	0.75-1.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Single Row Female Connector Assemblies	<u>33471</u>
MX150 Mat-Sealed Dual Row Female Connector Assemblies	<u>33472</u>

Application Tooling

Global

Description	Part Number
Extraction Toolkit for MX150 Connectors	<u>2002220700</u>
PremiumGrade Hand Crimp Tool for MX150 Female Terminals, 22-18 AWG	<u>638116000</u>
PremiumGrade Hand Crimp Tool for MX150 Female Terminals for 1.00mm ² and 1.50mm ² Metric Wires	<u>638116100</u>
Hand Crimp Tool Metric 0.5 and 0.75	<u>638116200</u>
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	<u>638131500</u>
ServiceGrade Hand Crimp Tool for MX150 Crimp Terminals, 22-14 AWG	<u>640160133</u>

This document was generated on Mar 09, 2025