



Part Number : 894858003

Product Description : Universal Serial Bus (USB) Shielded I/O Type A Receptacle, Single Upright, Right-Angle, Terminal Length 2.50mm, Without Mylar, 0.76µm Gold (Au) Plating, Tray Package, Lead-Free

Series Number : 89485
Product Category : I/O Connectors

Status : Active

Documents & Resources

Drawings

Drawing 894858003_sd.pdf
Packaging Design Drawing PK-89485-002-001.pdf

3D Models and Design Files


3D Model 894858003_stp.zip

Specifications

Product Specification PS-89485-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	89485
Description	Universal Serial Bus (USB) Shielded I/O Type A Receptacle, Single Upright, Right-Angle, Terminal Length 2.50mm, Without Mylar, 0.76µm Gold (Au) Plating, Tray Package, Lead-Free
Application	Wire-to-Board
Comments	Without Mylar
Component Type	Receptacle
Product Family	USB Connectors: USB Type-A, USB Type-B, and USB Type-C Plugs and Receptacles
Product Name	USB
Standard	USB 2.0
Type	A
UPC	822348695874

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	750V AC (RMS)

Physical

Circuits (Loaded)	4
-------------------	---

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Mounting Style	Upright
Net Weight	2.261/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PC Tail Length	2.50mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	1.40mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	0° to +50°C
Termination Interface Style	Through Hole
Waterproof / Dustproof	No

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	2
Max-Temp	260

This document was generated on May 08, 2024