

**Part Number :** [351510314](#)

**Product Description :** VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue

**Series Number :** 35151

**Status :** Active

**Product Category :** Connector Housings

---

## Documents and Resources

### Drawings

[351510314\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[351500000AS\\_ENG-000.pdf](#)

[351500000AS\\_KOR-000.pdf](#)

[PK-35151-004-001.pdf](#)


[PS-35150-001-001.pdf](#)

[PS-35150-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	35151
Description	VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754834711

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	3
Color - Resin	Blue
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	No

Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	3.060/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	7.30mm
Pitch - Termination Interface	7.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<a href="#">2026500909</a>
VersaBlade Hybrid Receptacles Housings and TPAs	<a href="#">35150</a>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<a href="#">35524</a>

#### Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural	<a href="#">351500390</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Red	<a href="#">351500392</a>
VersaBlade Terminal Position	<a href="#">351500393</a>

Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow	
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Blue	<u>351500394</u>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<u>2270288400</u>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<u>2270298400</u>
VersaBlade Male Crimp Terminals	<u>35745</u>
VersaBlade Female Crimp Terminals	<u>35746</u>
VersaBlade Female Crimp Terminals	<u>35748</u>

---

This document was generated on Apr 21, 2026