

**Part Number :** [2026560021](#)

**Product Description :** 1.20mm Pitch, Pico-EZmate Slim PCB Header, Single Row, Vertical, Friction Lock, 2 Circuits

**Series Number :** 202656

**Status :** Obsolete

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[2026560021\\_sd.pdf](#)

[Symbol and Footprint \(Multi-Format\)](#)


### Specifications

[2026540000-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	202656
Description	1.20mm Pitch, Pico-EZmate Slim PCB Header, Single Row, Vertical, Friction Lock, 2 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Keyword	Pico-EZmate 1.2
Product Name	Pico-EZmate Slim
UPC	191128201674

### Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	50V AC (RMS)/DC

### Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes

Mated Height	1.20mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	22.640/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	1.20mm
Pitch - Termination Interface	1.20mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-25° to +85°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Pico-EZmate Slim Receptacle Housings	<u>202654</u>

---

This document was generated on Jun 06, 2026