



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T1	REVISED PER ECR-25-232476	02APR2025	SA	DSC

AMP WIRE RANGE	 Listed FILE E13288
12-10 AWG SOLID OR STRANDED	12 AWG STRANDED

- 1
- STAMP 6S AMP 12-10* APPROX AS SHOWN
2.
- WIRE INSULATION DIAMETER:
ø2.667[.105] TO ø5.080[.200]
3.
- BODY MATERIAL THK: 1.016±0.051[.040±.002]
- 4
- MATERIAL:
BODY - BRASS PER ASTM B36
INSULATION - PVC
- 5
- FINISH:
BODY - TIN PALTE 0.00254[.000100]
MIN EXT THK PER ASTM B545
INSUALTION COLOR - YELLOW
- 6
- APPLIES FROM EDGE OF METAL WIRE BARREL TO
CENTER OF STUD HOLE



2500	ON TAPE, REEL	52961-1
500	LOOSE PIECE	52961
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			 TE Connectivity		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN L OLMEDA 26JUN95	
	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.127[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK M ELLIS 26JUN95	
FOR APPLICATION TOOLING INFORMATION	1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 		FINISH 		APVD G NGO 26JUN95	
									NAME TERMINAL, SPRING SPADE, SHORT, PLASTI-GRIP WIRE SIZE: 12-10 AWG	
									PRODUCT SPEC UL 486A-B	
									APPLICATION SPEC 114-2161	
									WEIGHT -	
									SIZE A3	
									CAGE CODE 00779	
									DRAWING NO C-52961	
									RESTRICTED TO -	
									SCALE 6:1	
									SHEET 1 OF 1	
									REV T1	
CUSTOMER DRAWING										