








P.C.B. LAYOUT



CIRCUIT DIAGRAM



Compliance: RohS III (2015/863/EU)

Tolerances: ±0.20mm			Date	Name
			01/12	dr
Dimension	08/20	dr	knitter-switch	
Rename	04/12	dr		
Modifications	Date	Name		

TSSE 623 x-RA

30 25 25


Page

1/2

Specifications:

Contact rating:	50mA, 12V DC
Contact resistance:	100mOhm max.
Insulation resistance:	100MOhm min. at 500V DC for 1 minute
Dielectric strength:	250V AC (50Hz or 60Hz) for 1 minute
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Mechanical life:	500 000 cycles
Travel:	0.45 +/-0.2mm
Material:	Cover: nickel silver
	Sealed rubber: silicone rubber hardness: 70°-60°
	Contact: phosphor bronze, silver plated
	Terminal: brass, silver plated
	Base: high-temp. thermoplastic PA9T UL94V-0, molded black

Soldering conditions:



x	Operating force (gf)	Stem colour
R	260 +/-70	red
N	180 +/-50	brown
RK	260 +/-70	black
NK	180 +/-50	black

Compliance: RohS III (2015/863/EU)

Tolerances: ±0.20mm			Date	Name	TSSE 623 x-RA	
			01/12	dr		
Dimension	08/20	dr	knitter-switch		30 25 25	
Rename	04/12	dr				
Modifications	Date	Name				

Page 2/2