**Part Number :** 731710560
**Product Description :** BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, Die Cast Body, Nickel (Ni) Plated, Housing Height 12.70mm, Nut and Lockwasher Included, Tray, 75 Ohms
**Series Number :** 73171
**Status :** Active
**Product Category :** RF / Coaxial Connectors



## Documents and Resources

### Drawings

731710560_sd.pdf

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | RF / Coaxial Connectors |
| Series | 73171 |
| Description | BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, Die Cast Body, Nickel (Ni) Plated, Housing Height 12.70mm, Nut and Lockwasher Included, Tray, 75 Ohms |
| Application | RF |
| Comments | 12.70mm Profile |
| Product Name | BNC |
| Style | PCB |
| Type | Miniature |
| UPC | 800753921580 |

### Electrical

| | |
|---|---|
| Frequency | 4 GHz |
| Impedance | 75Ω |
| Power / Voltage | VOLTAGE: 500 Vrms@Sea Level |

### Physical

| | |
|---|---|
| Cable Attachment | N/A |
| Gender | Jack |
| Keying to Mating Part | N/A |
| Net Weight | 17.883/g |
| Orientation | Right Angle |
| Packaging Type | Tray |

Downloaded from Arrow.com.

| | |
|---|---|
| Panel Mount | Yes |
| Panel Mount Method | Bulkhead |
| PCB Mounting | Through Hole |
| PCB Thickness - Recommended | 5.40mm |
| Reverse Polar | No |
| Wire/Cable Type | N/A |

**Solder Process Data**

| | |
|---|---|
| Max-Duration | 10 |
| Lead-Free Process Capability | WAVE |
| Max-Cycle | 2 |
| Max-Temp | 245 |



Downloaded from Arrow.com.