SIEMENS

Data sheet 5SJ4106-7HG42



Figure similar

Circuit breaker 10kA, 1-pole, C, 6A according to UL 489-277V

Model	
product brand name	SENTRON
product designation	Miniature circuit breakers
design of the product	Miniature circuit-breaker 5SJ4
General technical data	
number of poles	1
design of pole	1P
tripping characteristic class	C
mechanical service life (operating cycles) typical	10 000
installation environment regarding EMC	Suitable for environment B (immunity to interference not applicable)
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750	F
overvoltage category	3
degree of pollution	3
Voltage	
insulation voltage (Ui) at AC rated value	440 V
● operational current	
— at 30 °C rated value	6 A
— at 40 °C rated value	6 A
— at 50 °C rated value	5.7 A
— at 55 °C rated value	5.6 A
— at 60 °C rated value	5.4 A
● operational current at AC rated value	6 A
Supply voltage	
supply voltage	
● at AC	400 V
● at DC rated value	60 V
operating voltage	
● at AC according to UL 489 and CSA C22.2 No. 5-02 maximum	277 V
● at DC rated value maximum	60 V
● at DC 1-channel according to UL 489 and CSA C22.2 No. 5-02 maximum	60 V
● at DC 2-channel according to UL 489 and CSA C22.2 No. 5-02 maximum	125 V
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP 0 in the handle range

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

Breaking Capacity	
switching capacity current	
● according to EN 60898 rated value	10 kA
● according to IEC 60947-2 rated value	15 kA
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	2.7 W
Main circuit	
type of voltage supply at AC according to UL 489 and CSA C22.2 No. 5-02	480/277
suitability for operation	Infrastructure / Industry
Product details	
product feature touch protection	Yes
product component	
● **tunnel terminals top**	No
● **tunnel terminals bottom**	No
● combined terminal top	Yes
● combined terminal bottom	Yes
● neutral conductor switching	No
product feature halogen-free	Yes
product feature sealable	Yes
product feature silicon-free	Yes
product extension installable supplementary devices	Yes
Product function	
set values setting current (Ii) for I-tripping	7,5
reference value setting current (Ii) for I-tripping	x In
product function note	Terminal tightening torque for Cu, 60/75°C; 3.5Nm/31lb.in
Short circuit	
short-circuit current breaking capacity (Icn) at AC according to UL 1077 and CSA C22.2 No.235	10 kA
Connections	
connectable conductor cross-section finely stranded with core end processing	
● minimum	0.75 mm²
● maximum	25 mm²
tightening torque with screw-type terminals maximum	3.5 N·m
position of power supply cord	Any
Mechanical Design	
height	121 mm
width	18 mm
depth	70 mm
installation depth	70 mm
number of modular width units	1
fastening method	on standard mounting rail
mounting position	any
Net Weight	175 g
Environmental conditions	
standard	IEC / EN 60947-2 / UL 489
vibration resistance	50 m/s² at 25 to 150Hz and 60m/s² at 35Hz (4sec)
vibration resistance according to IEC 60068-2-6	±1 mm at 5 to 25 Hz; 50 m/s² at 25 to 150 Hz
ambient temperature during operation	
● minimum	-25 °C
● maximum	55 °C
ambient temperature during operation	max. 95% humidity
ambient temperature during storage	
● minimum	-40 °C
● maximum	75 °C
Approvals Certificates	
Environment	**General Product Approval**

© Copyright Siemens
Downloaded from Arrow.com.

Environmental Confirmations

Environmental Confirmations

General Product Approval	Test Certificates
	Special Test Certificate

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875

Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012

Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SJ4106-7HG42

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/5SJ4106-7HG42


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SJ4106-7HG42

CAx-Online-Generator
https://www.siemens.com/cax

Tender specifications
https://www.siemens.com/specifications

Characteristic curves
https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod__no>

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.



last modified: 1/11/2026

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.