



Part Number : [757840160](#)
Product Description : 0.80mm Pitch, iPass I/O Surface Mount Receptacle, Vertical, Internal Assembly with Shell, 36 Circuit, 0.76µm Gold (Au), Through Hole Option, Tail Length 3.56mm, Universal Key
Series Number : 75784
Status : Active
Product Category : High-Speed I/O Connectors



Documents & Resources


Drawings
[757840160_sd.pdf](#)
[PK-75784-001-001.pdf](#)

3D Models and Design Files
[757840160_stp.zip](#)
[EE-75577-001-001.pdf](#)
[SP-75577-001-001.zip](#)

Specifications
[AS-75783-001-001.pdf](#)
[PS-75783-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	75784
Description	0.80mm Pitch, iPass I/O Surface Mount Receptacle, Vertical, Internal Assembly with Shell, 36 Circuit, 0.76µm Gold (Au), Through Hole Option, Tail Length 3.56mm, Universal Key
Application	Wire-to-Board
Comments	Positive or passive latching cable available
Component Type	Receptacle
Product Name	iPass,Mini Multi-Lane,PCI Express
Type	Pluggable
UPC	822350356282

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Zinc, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.996/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PC Tail Length	3.56mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.18mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Surface Mount and Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Use with Part(s)

Description	Part Number
iPass Cable Assemblies	<u>74573</u>
Internal iPass Mini SAS Double-Ended Plugs	<u>79576</u>

This document was generated on Feb 07, 2025