


FLORENCE2-Z60

~60° wide beam

SPECIFICATION:

Dimensions	285.0 x 64.2
Height	8.1 mm
Fastening	screw
ROHS compliant	yes 





MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
FLORENCE2-Z60	Linear lens	PMMA	clear		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
F16008_FLORENCE2-Z60 » Box size: 398 x 298 x 140 mm	78	18	6	4.8



See also our general installation guide: www.ledil.com/installation_guide

Last update: 17/03/2025


Subject to change without prior notice

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):




LED J Series 2835
FWHM / FWTM 56.0° / 75.0°
Efficiency 96 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

FRANK


LED LED-Modul 280 x 55 mm 1B
FWHM / FWTM 48.0° / 73.0°
Efficiency 95 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

FRANK

LED LED-Modul 280 x 55 mm 2F
FWHM / FWTM 51.0° / 75.0°
Efficiency 95 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

inventronics



LED PL-BAR-G3 1100 280x55
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 96 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

LUMILEDS


LED LUXEON 5050 Round LES
 FWHM / FWTM 58.0° / 99.0°
 Efficiency 93 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

LUMILEDS

LED LUXEON XR-3535L (L202 - xxxx033C30001)
 FWHM / FWTM 56.0° / 75.0°
 Efficiency 97 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED NFSW757H
 FWHM / FWTM 56.0° / 77.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED Duris E5
 FWHM / FWTM 56.0° / 78.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Duris S8
 FWHM / FWTM 62.0° / 96.0°
 Efficiency 94 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo LED Line VO 1ft MF 3R HV5
 FWHM / FWTM 44.0° / 67.0°
 Efficiency 96 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS


LED Fortimo LED Line 1ft 1100lm 3R HV4
 FWHM / FWTM 57.0° / 77.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS

LED Fortimo LED Line 1ft 650lm 3R HV4 & LV4
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo LED Line 1ft HF 3R HV5
 FWHM / FWTM 46.0° / 69.0°
 Efficiency 96 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS


LED Fortimo LED Line 1ft LF 3R HV5 & LV5
 FWHM / FWTM 53.0° / 75.0°
 Efficiency 97 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS

LED Fortimo LED Line 1ft MF 3R HV5 & LV5
 FWHM / FWTM 46.0° / 69.0°
 Efficiency 96 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG


LED LM28xB Series
FWHM / FWTM 53.0° / 74.0°
Efficiency 92 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG



LED LM561B Plus
FWHM / FWTM 54.0° / 75.0°
Efficiency 94 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files


SAMSUNG

LED LT-R286A
FWHM / FWTM 55.0° / 76.0°
Efficiency 94 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files


OPTICAL RESULTS (MEASURED):



OPTICAL RESULTS (SIMULATED):




LED J Series 2835
 FWHM / FWTM 53.0° / 72.0°
 Efficiency 93 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 2
 Light colour/type White
 Required components:



Light distribution files




LED LUXEON 3030 2D (Square LES)
 FWHM / FWTM 50.0° / 68.0°
 Efficiency 92 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON 5050 Round LES
 FWHM / FWTM 58.0° / 79.0°
 Efficiency 90 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON 5050 Square LES
 FWHM / FWTM 60.0° / 81.0°
 Efficiency 90 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED Duris S5 (Single chip)
 FWHM / FWTM 50.0° / 68.0°
 Efficiency 92 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LH351D
 FWHM / FWTM 65.0° / 84.0°
 Efficiency 92 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LM28xB Series
 FWHM / FWTM 54.0° / 75.0°
 Efficiency 87 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Protective plate, glass



Light distribution files

SAMSUNG


LED LM301B
 FWHM / FWTM 64.0° / 116.0°
 Efficiency 90 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 2
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG

LED LM301B
 FWHM / FWTM 50.0° / 70.0°
 Efficiency 92 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LM302Z
 FWHM / FWTM 60.0° / 78.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG


LED LM302Z plus
 FWHM / FWTM 64.0° / 114.0°
 Efficiency 90 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 2
 Light colour/type White
 Required components:



Light distribution files



SAMSUNG

LED LM302Z plus
 FWHM / FWTM 52.0° / 71.0°
 Efficiency 92 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:






Light distribution files




OPTICAL RESULTS (SIMULATED):




OPTICAL RESULTS (SIMULATED):



OPTICAL RESULTS (SIMULATED):



OPTICAL RESULTS (SIMULATED):



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)