

LSA1A-2D

(Home (/index.php?ci_id=3972&la_id=1) : Products (/products) : Active Product Family 10-Oct-2006 : MICRO SWITCH™ Limit Switches : MICRO SWITCH™ Heavy-Duty Limit Switches : HDLS)

Distributor Inventory

Input part number for stock availability

Narrow Your Search

Modify Your Search

Products

Technology

Industries Served

Sales & Service

Distributor Inventory

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Availability	Global
Operating Force (OF)	0,45 N m [4 in lb] max.
Pretravel (PT)	15° max.
Overtravel (OT)	60° min.
Differential Travel (DT)	5° max.
Product Type	MICRO SWITCH™ Heavy-Duty Limit Switches
Actuator	Side Rotary
Lever Type	1.5 in to 3.5 in Adjustable Length Lever with front mounted Steel Rollers (.75 in dia. x .25 in wide)
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	HDLS Plug-in
Series Name	HDLS
Sealing	NEMA 1, 3, 4, 4X, 6, 6P, 12, 13
UL File #	E37138
Operating Temperature	-12 °C to 121 °C [10 °F to 250 °F]
Comment	Lever Included
Agency Approvals and Standards	UL, CE, CSA, CCC. EN60947-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

Product Search

Product Type:

Industry:

Search Term:

☐ New Products Only

☒ Entire Product Catalog

Search

My Links

[eCOM Login \(/index.php?ci_id=50629&la_id=1\)](/index.php?ci_id=50629&la_id=1)

[Request Access to eCOM \(/ecom access request\)](/ecom access request)

[Rep/AD Portal Login \(/index.php?ci_id=50606&la_id=1\)](/index.php?ci_id=50606&la_id=1)

[Rep/AD Portal Access Request \(/index.php?ci_id=50630&la_id=1\)](/index.php?ci_id=50630&la_id=1)

[Sample Request \(/sample request\)](/sample request)

[Digital U - HWL Learning Hub Login \(/index.php?ci_id=50607&la_id=1\)](/index.php?ci_id=50607&la_id=1)

[Digital U - HWL Learning Hub Access Request \(/index.php?ci_id=146099&la_id=1\)](/index.php?ci_id=146099&la_id=1)

[YouTube \(/www.youtube.com/user/SensingAndControl\)](https://www.youtube.com/user/SensingAndControl)

[Supplier Microsite \(/index.php?ci_id=50631&la_id=1\)](/index.php?ci_id=50631&la_id=1)

[Supplier Microsite \(/index.php?ci_id=44887&la_id=1\)](/index.php?ci_id=44887&la_id=1)

Literature and Media

[Data Sheets \(/white paper and technical data sheets library\)](/white paper and technical data sheets library)

[Videos \(/videos\)](/videos)

[Literature \(/literature\)](/literature)

[Literature Request \(/index.php?ci_id=50636&la_id=1\)](/index.php?ci_id=50636&la_id=1)

[White Papers \(/white papers\)](/white papers)

[Application Notes \(/application notes\)](/application notes)

[Application Demos \(/index.php?ci_id=141383&la_id=1\)](/index.php?ci_id=141383&la_id=1)

[CAD Renderings \(/cad renderings\)](/cad renderings)

Contacts

[Customer Service \(/index.php?ci_id=50608&la_id=1\)](/index.php?ci_id=50608&la_id=1)

[Technical Support \(/index.php?ci_id=50609&la_id=1\)](/index.php?ci_id=50609&la_id=1)

[Global Sales & Service \(/index.php?ci_id=50610&la_id=1\)](/index.php?ci_id=50610&la_id=1)

[Website Feedback \(/index.php?ci_id=142628&la_id=1\)](/index.php?ci_id=142628&la_id=1)

[Twitter \(/twitter.com/HONSensorSwitch\)](https://twitter.com/HONSensorSwitch)

[Terms & Conditions \(/index.php?ci_id=2588&la_id=1\)](/index.php?ci_id=2588&la_id=1)

[Privacy Statement \(/index.php?ci_id=2589&la_id=1\)](/index.php?ci_id=2589&la_id=1)

[Site Map \(/sitemap\)](/sitemap)