


REV.	DATE	ECR NO.	DESCRIPTION
NC	04/13/08	—	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	04/13/08										
7						CHECKED												
6						PART DESCRIPTION					SMA R/A BULKHEAD RECEPTACLE							
5	HEX NUT	BRASS	GOLD	1		ISSUED												
4	LOCK WASHER	BRASS	GOLD	1		SHEET	1	OF	1									
3	CONTACT PIN	BER. COPPER	GOLD	1		PART NO.					132203–16							
2	INSULATOR	PTFE	NATURAL	1														
1	HOUSING/BODY	BRASS	GOLD	1														
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE					DWG. NO.		132203–16.DWG	REV.	NC	SIZE	A	SCALE
					C:/132/132203–16.DWG													