



Part Number : [5037630591](#)
Product Description : 1.00mm Pitch, Pico-Lock PCB Header, Single Row, Right-Angle, Surface Mount, Gold over Nickel Plating, Positive Lock, 5 Circuits, Tape and Reel
Series Number : 503763
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[5037630591 sd.pdf](#)

3D Models and Design Files

[5037630591.dxf](#)

[5037630591 stp.zip](#)

Specifications

[AS-503764-001-001.pdf](#)


[SPK-503763-001-001.pdf](#)

[5037641001-PS-000.pdf](#)

[PS-503764-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	503763
Description	1.00mm Pitch, Pico-Lock PCB Header, Single Row, Right-Angle, Surface Mount, Gold over Nickel Plating, Positive Lock, 5 Circuits, Tape and Reel
Application	Signal, Wire-to-Board
Comments	See Molex product specification PS-503764-001 for additional current de-rating information
Component Type	PCB Header
Product Name	Pico-Lock
UPC	191128847049

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.5A
-------------------------------	------

Voltage - Maximum	150V AC (RMS)/DC
-------------------	------------------

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Mated Height	1.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	91.080/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.100µm
Polarized to Mating Part	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.00mm Pitch, Pico-Lock Single Row	<u>503764</u>

Receptacle Housings	
---------------------	--

This document was generated on May 25, 2025