

# DATA SHEET

## TRANSIENT VOLTAGE SUPPRESSORS

### AC/DC POWER SUPPLY

#### SMBJ-AT series

RoHS compliant & Halogen free

Product specification— June 15, 2022 V.3



## Transient Voltage Suppressors (TVS) Data Sheet

### Features

- For surface mounted applications in order to optimize board space
- Low profile package
- Built-in strain relief
- Glass passivated junction
- Low inductance
- Excellent clamping capability
- 600W peak pulse power capability at 10/1000μs waveform, repetition rate (duty cycle): 0.01%
- Fast response time
- Typical  $I_R$  less than 1μA above 12V
- High Temperature soldering: 260°C/10 seconds at terminals
- Plastic package has underwriters laboratory flammability 94V-0
- Meets MSL level 1, per J-STD-020
- Safety certification: UL: E244458
- AEC-Q101 qualified
- IEC61000-4-2 ESD 30KV Air, 30KV contact compliance



### Mechanical Data

- Case: JEDEC DO-214AA. Molded plastic over glass passivated junction
- Terminal: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode except bi-directional models
- Standard Packaging: 12mm tape (EIA STD RS-481)
- Weight: 0.10g

### Applications

- I/O interface
- AC/DC power supply
- Low frequency signal transmission line (RS232, RS485, etc.)

### Maximum Ratings and Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.


| Rating                                                                                                            | Symbol          | Value       | Units |
|-------------------------------------------------------------------------------------------------------------------|-----------------|-------------|-------|
| Peak pulse power dissipation at 10/1000μs waveform (Note1, Note2, Fig.1)                                          | $P_{PPM}$       | Minimum 600 | Watts |
| Peak pulse current of at 10/1000μs waveform (Note 1, Fig.3)                                                       | $I_{PPM}$       | See Table   | Amps  |
| Steady state power dissipation at $T_A=50^\circ\text{C}$ (Fig.5)                                                  | $P_{M(AV)}$     | 5.0         | Watts |
| Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load, (JEDEC Method) (Note3, Fig.6) | $I_{FSM}$       | 100         | Amps  |
| Operating junction and Storage Temperature Range.                                                                 | $T_J, T_{STG}$  | -55 to +150 | °C    |
| Typical thermal resistance junction to lead                                                                       | $R_{\theta JL}$ | 20          | °C/W  |
| Typical thermal resistance junction to ambient                                                                    | $R_{\theta JA}$ | 100         | °C/W  |

Notes: 1. Non-repetitive current pulse, per Fig.3 and derated above  $T_A=25^\circ\text{C}$  per Fig.2.

2. Mounted on 5.0mm×5.0mm (0.03mm thick) copper pads to each terminal.

3. 8.3ms single half sine-wave, or equivalent square wave, duty cycle=4 pulses per minutes maximum.

### Dimensions (SMB/DO-214AA)

| Product:                                                                                                                           | Symbol | Millimeters |       | Inches |       |
|------------------------------------------------------------------------------------------------------------------------------------|--------|-------------|-------|--------|-------|
|                                                                                                                                    |        | Min.        | Max.  | Min.   | Max.  |
|  <p>Product:</p> <p>Cathode Band</p> <p>Pad:</p> | L      | 4.06        | 4.57  | 0.160  | 0.180 |
|                                                                                                                                    | D      | 3.30        | 3.94  | 0.130  | 0.155 |
|                                                                                                                                    | D1     | 1.95        | 2.20  | 0.077  | 0.086 |
|                                                                                                                                    | T      | 5.21        | 5.59  | 0.205  | 0.220 |
|                                                                                                                                    | T1     | 0.76        | 1.52  | 0.030  | 0.060 |
|                                                                                                                                    | d      | -           | 0.203 | -      | 0.008 |
|                                                                                                                                    | H      | 2.15        | 2.65  | 0.085  | 0.104 |
|                                                                                                                                    | H1     | 2.13        | 2.47  | 0.084  | 0.097 |

### Electrical Characteristics (T<sub>A</sub>=25°C)

| Part Number    |               | Device Marking Code |    | Reverse Stand-Off Voltage | Breakdown Voltage @I <sub>T</sub> | Test Current        | Maximum Clamping Voltage @I <sub>PP</sub> | Peak Pulse Current  | Reverse Leakage @V <sub>RWM</sub> |
|----------------|---------------|---------------------|----|---------------------------|-----------------------------------|---------------------|-------------------------------------------|---------------------|-----------------------------------|
| Unidirectional | Bidirectional | UNI                 | BI | V <sub>RWM</sub> (V)      | V <sub>BR</sub> (V)               | I <sub>T</sub> (mA) | V <sub>C</sub> (V)                        | I <sub>PP</sub> (A) | I <sub>R</sub> (μA)               |
| SMBJ5.0A-AT    | SMBJ5.0CA-AT  | KE                  | AE | 5.0                       | 6.40~7.00                         | 10                  | 9.2                                       | 65.3                | 800                               |
| SMBJ6.0A-AT    | SMBJ6.0CA-AT  | KG                  | AG | 6.0                       | 6.67~7.37                         | 10                  | 10.3                                      | 58.3                | 800                               |
| SMBJ6.5A-AT    | SMBJ6.5CA-AT  | KK                  | AK | 6.5                       | 7.22~7.98                         | 10                  | 11.2                                      | 53.6                | 500                               |
| SMBJ7.0A-AT    | SMBJ7.0CA-AT  | KM                  | AM | 7.0                       | 7.78~8.60                         | 10                  | 12.0                                      | 50.0                | 200                               |
| SMBJ7.5A-AT    | SMBJ7.5CA-AT  | KP                  | AP | 7.5                       | 8.33~9.21                         | 1                   | 12.9                                      | 46.6                | 100                               |
| SMBJ8.0A-AT    | SMBJ8.0CA-AT  | KR                  | AR | 8.0                       | 8.89~9.83                         | 1                   | 13.6                                      | 44.2                | 50                                |
| SMBJ8.5A-AT    | SMBJ8.5CA-AT  | KT                  | AT | 8.5                       | 9.44~10.40                        | 1                   | 14.4                                      | 41.7                | 20                                |
| SMBJ9.0A-AT    | SMBJ9.0CA-AT  | KV                  | AV | 9.0                       | 10.00~11.10                       | 1                   | 15.4                                      | 39.0                | 10                                |
| SMBJ10A-AT     | SMBJ10CA-AT   | KX                  | AX | 10.0                      | 11.10~12.30                       | 1                   | 17.0                                      | 35.3                | 5                                 |
| SMBJ11A-AT     | SMBJ11CA-AT   | KZ                  | AZ | 11.0                      | 12.20~13.50                       | 1                   | 18.2                                      | 33.0                | 1                                 |
| SMBJ12A-AT     | SMBJ12CA-AT   | LE                  | BE | 12.0                      | 13.30~14.70                       | 1                   | 19.9                                      | 30.2                | 1                                 |
| SMBJ13A-AT     | SMBJ13CA-AT   | LG                  | BG | 13.0                      | 14.40~15.90                       | 1                   | 21.5                                      | 28.0                | 1                                 |
| SMBJ14A-AT     | SMBJ14CA-AT   | LK                  | BK | 14.0                      | 15.60~17.20                       | 1                   | 23.2                                      | 25.9                | 1                                 |
| SMBJ15A-AT     | SMBJ15CA-AT   | LM                  | BM | 15.0                      | 16.70~18.50                       | 1                   | 24.4                                      | 24.6                | 1                                 |
| SMBJ16A-AT     | SMBJ16CA-AT   | LP                  | BP | 16.0                      | 17.80~19.70                       | 1                   | 26.0                                      | 23.1                | 1                                 |
| SMBJ17A-AT     | SMBJ17CA-AT   | LR                  | BR | 17.0                      | 18.90~20.90                       | 1                   | 27.6                                      | 21.8                | 1                                 |

## Transient Voltage Suppressors

SMBJ-AT

8

| SMBJ18A-AT     | SMBJ18CA-AT   | LT                  | BT | 18.0                      | 20.00~22.10                       | 1                   | 29.2                                      | 20.6                | 1                                 |
|----------------|---------------|---------------------|----|---------------------------|-----------------------------------|---------------------|-------------------------------------------|---------------------|-----------------------------------|
| Part Number    |               | Device Marking Code |    | Reverse Stand-Off Voltage | Breakdown Voltage @I <sub>T</sub> | Test Current        | Maximum Clamping Voltage @I <sub>PP</sub> | Peak Pulse Current  | Reverse Leakage @V <sub>RWM</sub> |
| Unidirectional | Bidirectional | UNI                 | BI | V <sub>RWM</sub> (V)      | V <sub>BR</sub> (V)               | I <sub>T</sub> (mA) | V <sub>C</sub> (V)                        | I <sub>PP</sub> (A) | I <sub>R</sub> (μA)               |
| SMBJ20A-AT     | SMBJ20CA-AT   | LV                  | BV | 20.0                      | 22.20~24.50                       | 1                   | 32.4                                      | 18.6                | 1                                 |
| SMBJ22A-AT     | SMBJ22CA-AT   | LX                  | BX | 22.0                      | 24.40~26.90                       | 1                   | 35.5                                      | 16.9                | 1                                 |
| SMBJ24A-AT     | SMBJ24CA-AT   | LZ                  | BZ | 24.0                      | 26.70~29.50                       | 1                   | 38.9                                      | 15.5                | 1                                 |
| SMBJ26A-AT     | SMBJ26CA-AT   | ME                  | CE | 26.0                      | 28.90~31.90                       | 1                   | 42.1                                      | 14.3                | 1                                 |
| SMBJ28A-AT     | SMBJ28CA-AT   | MG                  | CG | 28.0                      | 31.10~34.40                       | 1                   | 45.4                                      | 13.3                | 1                                 |
| SMBJ30A-AT     | SMBJ30CA-AT   | MK                  | CK | 30.0                      | 33.30~36.80                       | 1                   | 48.4                                      | 12.4                | 1                                 |
| SMBJ33A-AT     | SMBJ33CA-AT   | MM                  | CM | 33.0                      | 36.70~40.60                       | 1                   | 53.3                                      | 11.3                | 1                                 |
| SMBJ36A-AT     | SMBJ36CA-AT   | MP                  | CP | 36.0                      | 40.00~44.20                       | 1                   | 58.1                                      | 10.4                | 1                                 |
| SMBJ40A-AT     | SMBJ40CA-AT   | MR                  | CR | 40.0                      | 44.40~49.10                       | 1                   | 64.5                                      | 9.3                 | 1                                 |
| SMBJ43A-AT     | SMBJ43CA-AT   | MT                  | CT | 43.0                      | 47.80~52.80                       | 1                   | 69.4                                      | 8.7                 | 1                                 |
| SMBJ45A-AT     | SMBJ45CA-AT   | MV                  | CV | 45.0                      | 50.00~55.30                       | 1                   | 72.7                                      | 8.3                 | 1                                 |
| SMBJ48A-AT     | SMBJ48CA-AT   | MX                  | CX | 48.0                      | 53.30~58.90                       | 1                   | 77.4                                      | 7.8                 | 1                                 |
| SMBJ51A-AT     | SMBJ51CA-AT   | MZ                  | CZ | 51.0                      | 56.70~62.70                       | 1                   | 82.4                                      | 7.3                 | 1                                 |
| SMBJ54A-AT     | SMBJ54CA-AT   | NE                  | DE | 54.0                      | 60.00~66.30                       | 1                   | 87.1                                      | 6.9                 | 1                                 |
| SMBJ58A-AT     | SMBJ58CA-AT   | NG                  | DG | 58.0                      | 64.40~71.20                       | 1                   | 93.6                                      | 6.5                 | 1                                 |
| SMBJ60A-AT     | SMBJ60CA-AT   | NK                  | DK | 60.0                      | 66.70~73.70                       | 1                   | 96.8                                      | 6.2                 | 1                                 |
| SMBJ64A-AT     | SMBJ64CA-AT   | NM                  | DM | 64.0                      | 71.10~78.60                       | 1                   | 103.0                                     | 5.9                 | 1                                 |
| SMBJ70A-AT     | SMBJ70CA-AT   | NP                  | DP | 70.0                      | 77.80~86.00                       | 1                   | 113.0                                     | 5.3                 | 1                                 |
| SMBJ75A-AT     | SMBJ75CA-AT   | NR                  | DR | 75.0                      | 83.30~92.10                       | 1                   | 121.0                                     | 5.0                 | 1                                 |
| SMBJ78A-AT     | SMBJ78CA-AT   | NT                  | DT | 78.0                      | 86.70~95.80                       | 1                   | 126.0                                     | 4.8                 | 1                                 |
| SMBJ85A-AT     | SMBJ85CA-AT   | NV                  | DV | 85.0                      | 94.40~104.00                      | 1                   | 137.0                                     | 4.4                 | 1                                 |
| SMBJ90A-AT     | SMBJ90CA-AT   | NX                  | DX | 90.0                      | 100.00~111.00                     | 1                   | 146.0                                     | 4.1                 | 1                                 |
| SMBJ100A-AT    | SMBJ100CA-AT  | NZ                  | DZ | 100.0                     | 111.00~123.00                     | 1                   | 162.0                                     | 3.7                 | 1                                 |
| SMBJ110A-AT    | SMBJ110CA-AT  | PE                  | EE | 110.0                     | 122.00~135.00                     | 1                   | 177.0                                     | 3.4                 | 1                                 |
| SMBJ120A-AT    | SMBJ120CA-AT  | PG                  | EG | 120.0                     | 133.00~147.00                     | 1                   | 193.0                                     | 3.1                 | 1                                 |
| SMBJ130A-AT    | SMBJ130CA-AT  | PK                  | EK | 130.0                     | 144.00~159.00                     | 1                   | 209.0                                     | 2.9                 | 1                                 |
| SMBJ150A-AT    | SMBJ150CA-AT  | PM                  | EM | 150.0                     | 167.00~185.00                     | 1                   | 243.0                                     | 2.5                 | 1                                 |
| SMBJ160A-AT    | SMBJ160CA-AT  | PP                  | EP | 160.0                     | 178.00~197.00                     | 1                   | 259.0                                     | 2.3                 | 1                                 |
| SMBJ170A-AT    | SMBJ170CA-AT  | PR                  | ER | 170.0                     | 189.00~209.00                     | 1                   | 275.0                                     | 2.2                 | 1                                 |
| SMBJ180A-AT    | SMBJ180CA-AT  | PT                  | ET | 180.0                     | 201.00~222.00                     | 1                   | 292.0                                     | 2.1                 | 1                                 |
| SMBJ190A-AT    | SMBJ190CA-AT  | PA                  | EC | 190.0                     | 211.00~233.00                     | 1                   | 308.0                                     | 2.0                 | 1                                 |
| SMBJ200A-AT    | SMBJ200CA-AT  | PV                  | EV | 200.0                     | 224.00~247.00                     | 1                   | 324.0                                     | 1.9                 | 1                                 |
| SMBJ210A-AT    | SMBJ210CA-AT  | PB                  | ED | 210.0                     | 237.00~263.00                     | 1                   | 340.0                                     | 1.8                 | 1                                 |
| SMBJ220A-AT    | SMBJ220CA-AT  | PX                  | EX | 220.0                     | 246.00~272.00                     | 1                   | 356.0                                     | 1.7                 | 1                                 |
| SMBJ250A-AT    | SMBJ250CA-AT  | PZ                  | EZ | 250.0                     | 279.00~309.00                     | 1                   | 405.0                                     | 1.5                 | 1                                 |
| SMBJ300A-AT    | SMBJ300CA-AT  | QE                  | FE | 300.0                     | 335.00~371.00                     | 1                   | 486.0                                     | 1.3                 | 1                                 |
| SMBJ350A-AT    | SMBJ350CA-AT  | QG                  | FG | 350.0                     | 391.00~432.00                     | 1                   | 567.0                                     | 1.1                 | 1                                 |
| SMBJ400A-AT    | SMBJ400CA-AT  | QK                  | FK | 400.0                     | 447.00~494.00                     | 1                   | 648.0                                     | 0.9                 | 1                                 |

|             |              |    |    |       |               |   |       |     |   |
|-------------|--------------|----|----|-------|---------------|---|-------|-----|---|
| SMBJ440A-AT | SMBJ440CA-AT | QM | FM | 440.0 | 492.00~543.00 | 1 | 713.0 | 0.9 | 1 |
|-------------|--------------|----|----|-------|---------------|---|-------|-----|---|

## Ratings and Characteristic Curves ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Figure 1. Peak Pulse Power Rating Curve




Figure 2. Pulse Derating Curve




Figure 3. Pulse Waveform




Figure 4. Typical Junction Capacitance




Figure 5. Steady State Power Dissipation Derating Curve






Figure 6. Maximum Non-Repetitive Forward Surge Current Uni-Directional Only



## Recommended Soldering Conditions


### Reflow Soldering




### Recommended Conditions

| Profile Feature                                                                                                                                                                                         | Pb-Free Assembly                 |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|
| Average ramp-up rate ( $T_L$ to $T_P$ )                                                                                                                                                                 | 3°C/second max.                  |
| Preheat <ul style="list-style-type: none"> <li>-Temperature Min (<math>T_{S\ min}</math>)</li> <li>-Temperature Max (<math>T_{S\ max}</math>)</li> <li>-Time (min to max) (<math>t_s</math>)</li> </ul> | 150°C<br>200°C<br>60-180 seconds |
| $T_{S\ max}$ to $T_L$ <ul style="list-style-type: none"> <li>-Ramp-up Rate</li> </ul>                                                                                                                   | 3°C/second max.                  |
| Time maintained above: <ul style="list-style-type: none"> <li>-Temperature (<math>T_L</math>)</li> <li>-Time (<math>t_L</math>)</li> </ul>                                                              | 217°C<br>60-150 seconds          |
| Peak Temperature ( $T_P$ )                                                                                                                                                                              | 260°C                            |
| Time within 5°C of actual Peak Temperature ( $t_P$ )                                                                                                                                                    | 20-40 seconds                    |
| Ramp-down Rate                                                                                                                                                                                          | 6°C/second max.                  |
| Time 25°C to Peak Temperature                                                                                                                                                                           | 8 minutes max.                   |

## Marking Code



## Part Number Code



## Ordering Code for Different Package

7 inch reel package: Add suffix “ /TR7 ” at the end of the part number, such as SMBJXXXCA-AT/TR7

13 inch reel package: Add suffix “ /TR13 ” at the end of the part number, such as SMBJXXXCA-AT/TR13

## Packaging

| Tape     | Symbol            | Dimension (mm) |
|----------|-------------------|----------------|
|          | W                 | 12.00±0.20     |
|          | P0                | 4.00±0.10      |
|          | P1                | 8.00±0.10      |
|          | P2                | 2.00±0.10      |
|          | D0                | Φ1.55±0.10     |
|          | D1                | Φ1.5±0.10      |
|          | E                 | 1.75±0.10      |
|          | F                 | 5.50±0.10      |
|          | A0                | 3.86±0.15      |
|          | B0                | 5.65±0.10      |
|          | K0                | 2.75±0.15      |
|          | T                 | 0.25±0.05      |
| 7" Reel  | D2                | Φ178.0±2.0     |
|          | D3                | Φ50.0Min.      |
|          | D4                | Φ13.0±0.5      |
|          | W1                | 16.0±2.0       |
|          | Quantity: 500PCS  |                |
| 13" Reel | D5                | Φ330.0±2.0     |
|          | D6                | Φ13.5±0.5      |
|          | H                 | 2.5±1.0        |
|          | W2                | 16.0±2.0       |
|          | Quantity: 3000PCS |                |