

Silicon Carbide (SiC) MOSFET - EliteSiC, 16 mohm 650 V, M3S, TO247-4L

NTH4L016N065M3S

$V_{(BR)DSS}$	$R_{DS(ON)}$ TYP	I_D MAX
650 V	16 mΩ @ V_{GS} = 18 V	71 A



N-CHANNEL MOSFET



TO-247-4LD
CASE 340CJ

Features

- Typical $R_{DS(on)}$ = 16 mΩ @ V_{GS} = 18 V
- Ultra Low Gate Charge ($Q_{G(tot)}$ = 100 nC)
- High Speed Switching with Low Capacitance (C_{oss} = 208 pF)
- 100% Avalanche Tested
- This Device is Halide Free and RoHS Compliant with Exemption 7a, Pb-Free 2LI (on second level interconnection)

Applications

- SMPS, Solar Inverters, UPS, Energy Storage, EV Charging Infrastructure

MAXIMUM RATINGS (T_J = 25 °C unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V_{DSS}	650	V
Gate-to-Source Static Voltage		V_{GS}	−10/+22.6	V
Gate-to-Source Transient Voltage	t_p < 0.5 μs, Duty Cycle ≤ 1%	V_{GS}	−11/+25	V
Continuous Drain Current	T_C = 25 °C	I_D	71	A
Power Dissipation		P_D	300	W
Continuous Drain Current	T_C = 100 °C	I_D	50	A
Power Dissipation		P_D	150	W
Pulsed Drain Current (Note 1)	T_C = 25 °C, t_p = 100 μs	I_{DM}	243	A
Continuous Source-Drain Current (Body Diode)	T_C = 25 °C, V_{GS} = −3 V	I_S	48	A
	T_C = 100 °C, V_{GS} = −3 V		28	
Pulsed Source-Drain Current (Body Diode) (Note 1)	T_C = 25 °C, V_{GS} = −3 V, t_p = 100 μs	I_{SM}	226	
Single Pulse Avalanche Energy (Note 2)	I_{LPK} = 60 A, L = 0.1 mH	E_{AS}	180	mJ
Operating Junction and Storage Temperature Range		T_J, T_{stg}	−55 to +175	°C
Lead Temperature for Soldering Purposes (1/8″ from case for 10 seconds)		T_L	270	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Single pulse, limited by max junction temperature.
2. E_{AS} of 180 mJ is based on starting T_J = 25 °C, L = 0.1 mH, I_{AS} = 60 A, V_{DD} = 100 V, V_{GS} = 18 V.

MARKING DIAGRAM



H4L016065M3S = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping
NTH4L016N065M3S	TO-247-4L	30 Units / Tube

© Semiconductor Components Industries, LLC, 2023

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Note 3)	$R_{\theta JC}$	0.50	°C/W

3. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Value	Unit
Operation Values of Gate-to-Source Voltage	V_{GSop}	−3/+18	V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA, T_J = 25 °C	650			V
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 650 V, T_J = 25 °C			10	μA
		V_{DS} = 650 V, T_J = 175 °C (Note 5)			500	
Gate-to-Source Leakage Current	I_{GSS}	V_{GS} = −10 V, V_{DS} = 0 V	−1			μA
		V_{GS} = +22.6 V, V_{DS} = 0 V			1	
ON CHARACTERISTICS						
Drain-to-Source On Resistance	$R_{DS(on)}$	V_{GS} = 18 V, I_D = 30 A, T_J = 25 °C		16	23.5	mΩ
		V_{GS} = 18 V, I_D = 30 A, T_J = 175 °C (Note 5)		25		
		V_{GS} = 15 V, I_D = 30 A, T_J = 25 °C		21		
		V_{GS} = 15 V, I_D = 30 A, T_J = 175 °C (Note 5)		27		
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 15 mA, T_J = 25 °C	2.0	2.7	4.0	V
Forward Transconductance	g_{FS}	V_{DS} = 10 V, I_D = 30 A (Note 5)		27		S
CHARGES, CAPACITANCES & GATE RESISTANCE						
Input Capacitance	C_{ISS}	V_{DS} = 400 V, V_{GS} = 0 V, f = 1 MHz (Note 5)		2735		pF
Output Capacitance	C_{OSS}			208		
Reverse Transfer Capacitance	C_{RSS}			18		
Total Gate Charge	$Q_{G(TOT)}$	V_{DD} = 400 V, I_D = 30 A, V_{GS} = −3/18 V (Note 5)		100		nC
Gate-to-Source Charge	Q_{GS}			33		
Gate-to-Drain Charge	Q_{GD}			25		
Gate Resistance	R_G	f = 1 MHz		3.0		Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	V_{GS} = −3/18 V, V_{DD} = 400 V, I_D = 30 A, R_G = 4.7 Ω, T_J = 25 °C (Notes 4, 5)		6.5		ns
Turn-Off Delay Time	$t_{d(OFF)}$			45		
Rise Time	t_r			20		
Fall Time	t_f			45		
Turn-On Switching Loss	E_{ON}			103		μJ
Turn-Off Switching Loss	E_{OFF}			100		
Total Switching Loss	E_{TOT}			203		

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	V_{GS} = −3/18 V, V_{DD} = 400 V, I_D = 30 A, R_G = 4.7 Ω, T_J = 175 °C (Notes 4, 5)		4.7		ns
Turn-Off Delay Time	$t_{d(OFF)}$			55		
Rise Time	t_r			20		
Fall Time	t_f			13		
Turn-On Switching Loss	E_{ON}			104		μJ
Turn-Off Switching Loss	E_{OFF}			108		
Total Switching Loss	E_{TOT}			212		
SOURCE-TO-DRAIN DIODE CHARACTERISTICS						
Forward Diode Voltage	V_{SD}	I_{SD} = 30 A, V_{GS} = −3 V, T_J = 25 °C		4.6	6.0	V
		I_{SD} = 30 A, V_{GS} = −3 V, T_J = 175 °C (Note 5)		4.3		
Reverse Recovery Time	t_{RR}	V_{GS} = −3 V, I_S = 30 A, dI/dt = 1000 A/μs, V_{DS} = 400 V, T_J = 25 °C (Note 5)		23		ns
Charge Time	t_a			13		
Discharge Time	t_b			10		
Reverse Recovery Charge	Q_{RR}			146		nC
Reverse Recovery Energy	E_{REC}			12		μJ
Peak Reverse Recovery Current	I_{RRM}			11		A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. E_{ON}/E_{OFF} result is with body diode.
5. Defined by design, not subject to production test.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. Output Characteristics




Figure 2. Output Characteristics




Figure 3. Output Characteristics




Figure 4. I_D vs. V_{GS}




Figure 5. $R_{DS(ON)}$ vs. V_{GS}




Figure 6. $R_{DS(ON)}$ vs. I_D

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. $R_{DS(ON)}$ vs. I_D




Figure 8. $R_{DS(ON)}$ vs. T_J




Figure 9. Capacitance Characteristics




Figure 10. Stored Energy vs. Drain-to-Source Voltage




Figure 11. Gate Charge Characteristics




Figure 12. Reverse Conduction Characteristics

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 13. Reverse Conduction Characteristics




Figure 14. Safe Operating Area




Figure 15. Avalanche Current vs Pulse Time (UIS)




Figure 16. Maximum Power Dissipation vs Case Temperature




Figure 17. E_{SW} vs. I_D




Figure 18. E_{SW} vs. I_D

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 19. E_{SW} vs. R_G




Figure 20. E_{SW} vs. R_G




Figure 21. E_{SW} vs. R_G




Figure 22. E_{SW} vs. R_G




Figure 23. E_{SW} vs. V_{DS}

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 24. Thermal Response Characteristics

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

REVISION HISTORY


Revision	Description of Changes	Date
0	Initial datasheet release	10/31/2025
1	Updated dynamic gate source voltage ratings in maximum ratings table	6/15/2026

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TO−247−4LD
CASE 340CJ
ISSUE A

DATE 16 SEP 2019



NOTES:

A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
B. DIMENSIONS ARE EXCLUSIVE OF BURRS,MOLD FLASH,AND TIE BAR EXTRUSIONS.
C. ALL DIMENSIONS ARE IN MILLIMETERS.
D. DRAWING CONFORMS TO ASME Y14.5-2009.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.80	5.00	5.20
A1	2.10	2.40	2.70
A2	1.80	2.00	2.20
b	1.07	1.20	1.33
b1	1.20	1.40	1.60
b2	2.02	2.22	2.42
c	0.50	0.60	0.70
D	22.34	22.54	22.74
D1	16.00	16.25	16.50
D2	0.97	1.17	1.37
e	2.54 BSC		
e1	5.08 BSC		
E	15.40	15.60	15.80
E1	12.80	13.00	13.20
E/2	4.80	5.00	5.20
L	18.22	18.42	18.62
L1	2.42	2.62	2.82
p	3.40	3.60	3.80
p1	6.60	6.80	7.00
Q	5.97	6.17	6.37
S	5.97	6.17	6.37

DOCUMENT NUMBER:	**98AON13852G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**TO−247−4LD**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.