
Part Number : 1700712011
Product Description : zSFP+ Stacked Ganged Assembly with Elastomeric Gasket, 2-by-2 with 4 Light Pipes, 80 Circuits
Series Number : 170071
Status : Active
Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

1700712011_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-170071-0001-001.zip

EE-170071-0001-001.pdf

SP-170426-1000-001.zip

Specifications

AS-170071-0002-001.pdf

PS-170071-0001-001.pdf

TS-170071-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-

Downloaded from Arrow.com.

	DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	170071
Description	zSFP+ Stacked Ganged Assembly with Elastomeric Gasket, 2-by-2 with 4 Light Pipes, 80 Circuits
Application	Module-to-Board
Component Type	Receptacle
Product Name	zSFP Plus,zSFP+
Type	Pluggable
UPC	884982402140

Agency

UL	E29179

Electrical

Current - Maximum per Contact	0.5A

Downloaded from Arrow.com.

Data Rate	28.0 Gbps
Shielded	Yes
Shield Type	N/A
Voltage - Maximum	30V AC

Physical

Circuits (Loaded)	80
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	51.854/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	4
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Downloaded from Arrow.com.

Lead-Free Process Capability	N/A

Application Tooling

Downloaded from Arrow.com.