



Part Number : [760935001](#)

**Product Description :** Small Form-factor Pluggable Plus (SFP+) Stacked 2-by-5 Multi-Port Connector with 4 Lightpipe Ports, Elastomeric Gasket, 200 Circuits, Tin (Sn) Tails

Series Number : 76093

Status : Active

Product Category : High-Speed I/O Connectors

---

## Documents & Resources

### Drawings

[Drawing 760935001\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 760935001\\_stp.zip](#)

[Electrical Model Document EE-76090-001-001.pdf](#)

[S-Parameter Model SP-76090-001-001.zip](#)

[Symbol Footprint Data SYM-76093-5001-001.zip](#)

### Specifications

[Application Specification AS-75310-001-001.pdf](#)

[Application Specification AS-76090-001-001.pdf](#)

[Packaging Specification PK-75733-001-001.pdf](#)


[Product Specification PS-75310-001-001.pdf](#)

[Test Summary TS-76092-999-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC

- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	High-Speed I/O Connectors
Series	76093
Description	Small Form-factor Pluggable Plus (SFP+) Stacked 2-by-5 Multi-Port Connector with 4 Lightpipe Ports, Elastomeric Gasket, 200 Circuits, Tin (Sn) Tails
Application	Module-to-Board
Component Type	Receptacle
Product Family	SFP+ and SFP Interconnect Solutions
Product Name	SFP Plus,SFP+
Type	Pluggable
UPC	800756878010

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	0.5A
Data Rate	10.0 Gbps, 28.0 Gbps
Grounding to Panel	None
Shield Type	EMI Gasket
Shielded	Yes

Voltage - Maximum	120V AC (RMS)/DC
-------------------	------------------

## Physical

Boot Color	N/A
Circuits Detail	200
Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black, Clear (Blue Tint)
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	121.061/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PC Tail Length	2.07mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	10
Temperature Range - Operating	-40° to +85°C

Termination Interface Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

---

This document was generated on Jul 30, 2024