


SS-5FH

Subminiature fast-acting fuses

**Product features:**

- Halogen free, lead free, RoHS compliant
- Fast-acting, high breaking capacity subminiature fuse
- Plastic cap and base, flammability UL 94V0
- Lead wire with tin-plated copper, diameter 0.6 mm
- Protects against harmful overcurrents in primary and secondary applications
- Small radial-leaded design minimizes board space and eliminates need for additional mounting components

Designed to UL 248-14

Applications

- Primary circuit protection for lighting ballasts
- LED Lighting primary protection
- High short-circuit current devices

Agency information

- cULus, File E19180, Guide JDYX/JDYX7

Ordering

- Specify product and packaging code (i.e., SS-5FH-3.15A-AP)

*Powering Business Worldwide*

Electrical characteristics

Amps	1.0 I_n	1.5 I_n	2.0 I_n
3.15 A	4 hours, min	10 minutes, max	2 minutes, max

Specifications


Part number	Voltage rating AC	Voltage rating DC	Interrupting rating (amps) @ rated voltage (50 Hz) AC ¹	Interrupting rating (amps) @ rated voltage DC	Typical DC cold resistance (mΩ) ²	Typical pre-arcig I ² t (A ² s) ³	Typical voltage drop @ 1 I_n (mV) ⁴	Max power dissipation @ 1 I_n (mW) ⁵	Agency information
									cULus
SS-5FH-3.15A	350	150	100	100	31.5	22.5	168	675	X

1. Interrupting ratings: measured at 100 A, 95% to 100% PF on AC.
2. Typical DC cold resistance (measured at <10% of rated current).
3. The typical I²t value is measured at 10 times of I_n.
4. Typical voltage drop @ 1 I_n (measured at +20 °C ambient temperature at rated current).
5. Maximum power dissipation (measured at +20 °C ambient temperature at rated current).

Packaging Codes


-BK	200 fuses in a polybag, lead length L = 4.3±0.3.
-AP	Ammo Pack, 1000 fuses, pitch = 12.7

Dimensions - mm [in]




BK Pack

Recommended pad layout



Pitch=5mm .


Time-current curves



Temperature derating curve

- Normal operating temperature: $+25^{\circ}\text{C} \pm 2^{\circ}\text{C}$
- Operating temperature range: -40°C to $+85^{\circ}\text{C}$ with proper correction factor applied

Correction factor chart




Soldering

Wave solder

Reservoir temperature: 260°C, Max.10Sec.

Recommended Profile



Manual solder

350 °C, 4-5Sec. (by soldering iron), generally manual, hand soldering is not recommended.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 10274 BU-SB14519
June 2017

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.

