

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_BNC-50-0-24/100_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration

Interface type	Gender	Standard
BNC	jack	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	Silver Plating
Washer	Bronze	Silver Plating

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data

Weight	0.0131 kg
Mating cycles	500
Flange type	round flange / dia. 16
Tab style	solder end

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_BNC-50-0-24/100_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22540321	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22540321	22_BNC-50-0-24/100_NE	Single

Additional Information	
Remarks	Hermetically sealed: leak rate $\leq 10^{-6}$ Torr l/s (atm cc/s) O-ring mount bulkhead feedthrough design, leak rate dependent on environmental condition, typ. $\leq 10^{-6}$ Torr l/s

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2820 / Date of publication: 12.07.2025 / uncontrolled copy