Part Number : 1202540043
Product Description : Contrinex Photoelectric Sensor, C23 (20 x 30mm) Housing, Background Suppression, 10 - 300mm Operating Distance, NPN, Changeover, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable
Series Number : 120254
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : LHR-C23PA-PMK-101



Documents and Resources

Specifications

1202540042-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Photoelectric Sensors
Series	120254
Description	Contrinex Photoelectric Sensor, C23 (20 x 30mm) Housing, Background Suppression, 10 - 300mm Operating Distance, NPN, Changeover, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable
IP Rating	IP67
Operating Principle	Background Suppression
Product Name	Contrinex
Type	Photoelectric
UPC	191130066995

Electrical

Output	Changeover
Polarity	NPN
Switching Frequency	≤ 1000 Hz

Physical

Connection	Cable (PVC 2m, 4-wire)
Housing Size	20 x 30mm
Material - Housing	ABS

Downloaded from Arrow.com.

Material - Window	PMMA
Operating Distance	10 - 300mm
Output	Changeover
Sensor Housing Size	C23
Temperature Range - Operating	-25° to +65°C

Downloaded from Arrow.com.