

Vectron International**Development specification****TFS1662****1/5****Measurement condition**

Ambient temperature T_A :	23	°C
Input power level:	0	dBm
Terminating impedance:		
Input:	50	Ω
Output:	50	Ω

Remark:

The reference level for the relative attenuation a_{rel} of the TFS1662 is the maximum attenuation in the pass band. The maximum attenuation in the pass band is defined as the insertion loss a_e . The nominal frequency f_N is fixed at 1662.5 MHz without any tolerance or limit. The values of relative attenuation a_{rel} are guaranteed over the whole operating temperature range. The frequency shift of the filter within the operating temperature range is included in the production tolerance scheme.

D a t a**typ. value****tolerance / limit**

Insertion loss		a_e		max.	3.5	dB
Nominal frequency		f_N	-		1662.5	MHz
Passband		PB	-	$f_N \pm$	12.5	MHz
Pass band variation		PBV		max.	2.0	dB
Relative attenuation		a_{rel}	-			
1000	MHz ... 1518	MHz		min.	23	dB
1518	MHz ... 1580	MHz		min.	30	dB
1580	MHz ... 1605	MHz		min.	20	dB
1605	MHz ... 1623	MHz		min.	20	dB
1705	MHz ... 1800	MHz		min.	17	dB
1800	MHz ... 3400	MHz		min.	25	dB
Return loss within PB				min.	8	dB
Input power level			-	max.	16	dBm
Operating temperature range		OTR	-		-40 °C ... +85 °C	
Storage temperature range			-		-55 °C ... +125 °C	
Temperature coefficient of frequency		TC_f *)	-42	ppm/K		

$$*) \Delta f = TC_f (T - T_A) f_N$$

Generated:**Checked / Approved:**

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com


Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Filter characteristic

t.b.d.


Construction and pin connection

(All dimensions in mm)



1	Input
2	Ground
3	Ground
4	Output
5	Ground
6	Ground

Date code:	Year + week
J	2017
K	2018
L	2019
...	

50 Ω Test circuit

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Stability characteristics, reliability

After the following tests the filter shall meet the whole specification:

1. Shock: 500 g, 1 ms, half sine wave, 3 shocks each plane;
DIN IEC 60068 T2 - 27
2. Vibration: 10 Hz to 2000 Hz, 0.35 mm or 5 g respectively, 1 octave per min, 10 cycles per plane, 3 planes; DIN IEC 60068 T2 - 6
3. Change of temperature: -55 °C to 125 °C / 15 min. each / 100 cycles
DIN IEC 60068 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;
5. SAW devices are Electrostatic Discharge (ESD) sensitive devices.

This filter is RoHS compliant (2011/65/EU)

Packing

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;
tape type II, embossed carrier tape with top cover tape on the upper side;


max. pieces of filters per reel:	3000
reel of empty components at start:	min. 300 mm
reel of empty components at start including leader:	min. 500 mm
trailer:	min. 300 mm

Tape (all dimensions in mm)

W	: 8.00 +0.3/-0.1
Po	: 4.00 ±0.1
Do	: 1.55 ±0.05
E	: 1.75 ±0.1
F	: 3.50 ±0.05
G(min)	: 0.75
P2	: 2.00 ±0.05
P1	: 4.00 ±0.1
D1(min)	: 1.00
Ao	: 1.80 ±0.05
Bo	: 2.25 ±0.05
Ct	: 5.30 ±0.1
Ko	: 0.90 ±0.05
t	: 0.30 ±0.05

Reel (all dimensions in mm)

A	: 330 or 180
W1	: 8.40 +1.5/-0
W2(max)	: 14.40
N(min)	: 60.00
C	: 13.0 ±0.2




The minimum bending radius is 45 mm.

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Air reflow temperature conditions

Conditions	Exposure
Average ramp-up rate (30 °C to 217 °C)	less than 3 °C / second
> 100 °C	between 300 and 600 seconds
> 150 °C	between 240 and 500 seconds
> 217 °C	between 30 and 150 seconds
Peak temperature	max. 260 °C
Time within 5 °C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50 °C)	less than 6 °C / second
Time from 30 °C to Peak temperature	no greater than 300 seconds

Chip-mount air reflow profile

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

History

Version	Reason of Changes	Name	Date
1.0	- Generation of development specification	C. Noack	08.05.2017
1.1	- Change data table (input power level)	C. Noack	30.05.2017

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.