Part Number : 22284037
Product Description : KK 254 Breakaway Header, Vertical, 3 Circuits, 0.76µm Gold (Au) Plating, Mating Pin Length 8.13mm, Bag
Series Number : 42375
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : 42375-0178



Documents and Resources

Drawings

022284037_sd.pdf

PK-40873-0041-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-10-07-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	42375
Description	KK 254 Breakaway Header, Vertical, 3 Circuits, 0.76µm Gold (Au) Plating, Mating Pin Length 8.13mm, Bag
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	KK 254
UPC	800754386074

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V

Downloaded from Arrow.com.

Physical

Breakaway	Yes
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.204/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.05mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	Unshrouded
Stackable	No
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Through Hole

Downloaded from Arrow.com.

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	2695
KK 254 Receptacle Housings	7880
KK 254 PC Board Connector	4455
2.54mm Pitch C-Grid Shunt Terminal Housings	7859

Downloaded from Arrow.com.