

# Image Sensors | AR1335

[Show Side Navigation](#)

## CMOS Image Sensor, 13 MP, 1/3"

[Availability & Samples](#)[Email Sales](#)[Favorite](#)[Request Datasheet](#)[CAD Model](#)[Overview](#)[Evaluation/Development Kits](#)[Technical Documentation](#)[Design Tools](#)[Training & Related](#)

## Overview

The AR1335 is a 1/3.2-inch CMOS active-pixel digital image sensor with a pixel array of 4208H x 3120V. The AR1335 digital image sensor, features breakthrough 1.1µm pixel technology that delivers superior low-light image quality through leading sensitivity, quantum efficiency and linear full well. This allows image quality that rivals digital still cameras. With a sensor architecture focused on low power and a high Chief Ray Angle (CRA) for low Z-heights, the AR1335 is ideal for smartphone and other mobile device applications. It incorporates sophisticated on-chip camera functions such as windowing, mirroring, column and row skip modes, and snapshot mode. It is programmable through a simple two-wire serial interface. The AR1335 sensor can generate full resolution image at up to 30 frames per second (fps) and supports advanced video modes including 4K 30fps, 1080P 60fps and 720P 120fps.

[Applications](#)[End Products](#)[Features](#)[Material Composition](#)[Product Change Notification](#)

## Availability & Samples

Search Table		Products: 7		Share	Export	Compare	Columns	Sort by Product
Product	Status	CAD Models	Compliance	Package Type	Case Outline	MSL Type	MSL Temp (°C)	
AR1335CSSM11SMKA0-CP	Active			ODCSP-63	570BU	4	245	
AR1335CSSC11SMKA0-CP	Active			ODCSP-63	570BU	4	245	
AR1335CSSC32SMD20	Active			-	-	NA	0	
AR1335CSSC11SMD20	Last Shipments			-	-	NA	0	
AR1335CSSC11SMKA0-CP1	Last Shipments			ODCSP-63	570BU	4	245	
AR1335CSSC11SMKA0-CP2	Last Shipments			ODCSP-63	570BU	4	245	
AR1335CSSM11SMD20	Last Shipments			-	-	NA	0	

Products per page 10

1-7 of 7

[About onsemi](#)[Locations](#)[Corporate Fact Sheet](#)[Quality and Reliability](#)[Ecosystem Partners](#)[Intellectual Property](#)[Leadership](#)[Investor Relations](#)[Events](#)[Governance](#)[Financials](#)[Stock Info](#)[News](#)[Resources](#)[News & Media](#)[Press](#)[Announcements](#)[In The News](#)[Blog](#)[Media Contacts](#)[Image Library](#)[Careers](#)[Search & Apply](#)[Early Careers](#)[Experienced Careers](#)[Internships](#)[Career Benefits](#)[Where We Are](#)[Who We Are](#)

Connect with us

[Language](#)[Do Not Sell or Share My Personal Information](#) | [Accessibility](#) | [Terms of Sale](#) | [Cookie Policy](#) | [Terms of Use](#) | [Privacy](#)[Subscribe](#) | [Site Map](#)