

Product Description

Tflex™ UT20000 is a specially formulated ultra-thin gap filler thermal interface material designed for thin interfaces that offers excellent thermal performance and high compliancy. It is designed without embedded reinforcing fiberglass to minimize contact resistance, yet still allows easy material handling and durability during assembly.

Tflex™ UT20000 provides excellent interfacing and its ability to wet out mating surfaces allows for efficient transfer of heat away from components. It is an ideal choice for low-pressure applications and optimum solution in handheld devices with thin interface gap and limited space requirements.

Tflex™ UT20000 is electrically non-conductive, stable from -50°C thru 200°C and offered in thicknesses that range from 0.008" (200 µm) up to 0.040" (1000 µm).

FEATURES AND BENEFITS


- Thermal Conductivity of 3.0 W/mK
- No fiberglass carrier to minimize thermal resistance, yet still easy to handle
- Excellent surface wetting for low contact resistance
- Unique formulation minimizes thermal resistance at low mounting forces
- Environmentally friendly solution that meets regulatory requirements including RoHS and REACH

SPECIFICATIONS

TYPICAL PROPERTIES	VALUE	TEST METHOD
Construction & Composition	Ceramic filled silicone sheet	N/A
Color	Grey	Visual
Thickness Range	200 µm (0.008")- 1000 µm (0.040")	N/A
Thermal Conductivity (W/mK)	3.0	Hot Disk
Density (g/cc)	3.2	Helium Pycnometer
Hardness (Shore 00)	83.3 (200-375) µm 56.4 (400-1000) µm	ASTM D2240
Outgassing TML (weight %)	0.34%	ASTM E595
Outgassing CVCN (weight %)	0.09%	ASTM E595
Temperature Range	-50°C to 200°C	Laird Test Method
Rth@ 200 µm, 10 psi, 50° C	0.25°C-in2/W	ASTM D5470
Dielectric Constant @ 1MHz	5.87	ASTM D150
UL Flammability Rating	V-0	UL 94
Volume Resistivity	2.2 x 10 ¹⁵ ohm-cm	ASTM D257

Americas: +1.866.928.8181
Europe: +49.(0).8031.2460.0
Asia: +86.755.2714.1166

www.lairdtech.com




AVAILABILITY

STANDARD THICKNESSES

- 0.008" (200 μ m) up to 0.020" (500 μ m) thick material available in 25 μ m increments
- Also available in 0.025" (625 μ m), 0.030" (750 μ m), 0.035" (875 μ m), 0.040" (1000 μ m)
- Available in standard sheet sizes of 18" x 18" and 9" x 9" or custom die cut parts. Custom die cut parts on a roll available for 200 μ m (0.008") thru 375 μ m (0.015")

PART NUMBER SYSTEM

Tflex™ indicates Laird elastomeric thermal gap filler product line. UT20000 indicates Tflex UT20000 product line with thickness in microns



EXAMPLES:

- Tflex™ UT20200= 200 μ m (0.008") thick Tflex™ UT20000 material
- Tflex™ UT20500= 500 μ m (0.020") thick Tflex™ UT20000 material

A17759-00 Tflex UT20000 DS 051419

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non-infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2013 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third-party intellectual property rights.