


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	50-00027	Connector, dc jack, 5.5x2.5xL17.4 mm, molding style	1	
2	30-00007	Wire, 2C BC, 18 AWG, UL2468, 300V, 80C, 4.4 mm, VW-1, PVC, 87A	1	
3	24-00004	Overmold, PVC, black	1	



Wiring diagram	
50-00027	Wire Color
Center	Black with stripe
Sleeve	Black

REVISION	DATE	DESCRIPTION	PREPARED:	NOTES	TENSILITY 20802 Sockeye Place #130 Bend, OR 97701 USA tel 541.323.3228 fax 541.323.4202 800 877.670.7118 www.tensility.com		
A	6/27/2012	Initial release	GL 2016.01.06 16:50:43 -08'00'	RoHS compliant			
			LA Digitally signed by LA, DN: cn=LA, o=Tensility, ou=Engineering, email=LA@Tensility.com, c=US Date: 2016.01.19 13:57:00 -0800	Function test: no open, no reversed polarity, no short circuit, no INT	7 A, 12 Vdc Functionally equivalent components may be used		
			DIMENSIONS ARE IN MILLIMETERS	DESCRIPTION:	SIZE	PART NUMBER	
			TOLERANCES:	Cable, 1830 mm, 5.5x2.5 mm 50-00027 dc jack to stripped tinned, 18 AWG, 30-00007 wire	A	10-01090	
			X: ± 0.5 mm		SCALE: 1:1	WEIGHT:	SHEET 1 OF 1
			X.X: ± 0.3 mm				
			X.XX: ± 0.05 mm				