


Part Number : [622018639](#)
Product Description : Press-In Tool for 6-Pair by 14-Column Backplane
Series Number : 207123
Status : Obsolete
Product Category : Application Tooling Accessories



Documents & Resources

Tooling Specifications

[ATS-622018639-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Application Tooling Accessories
Series	207123
Description	Press-In Tool for 6-Pair by 14-Column Backplane
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	883906616632
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Applicable Parts

Description	Part Number
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761451704</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761451705</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451706</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Left Endwall, 14 Columns, 252 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451716</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Left Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451717</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Left Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451718</u>

Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 14 Columns, 252 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761451723</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761451725</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 14 Columns, 252 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451726</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451727</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451728</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Right Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>761451737</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Right Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761451738</u>
Impact 100 Ohm 6 Pair Vertical	<u>761453704</u>

Backplane Header, Left Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	
Impact 100 Ohm 6 Pair Vertical Backplane Header, Left Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761453705</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Left Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761453707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Left Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761453708</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761455704</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761455705</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761455707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Right Guided,	<u>761455708</u>

Open Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	
Impact 100 Ohm 6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761457707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761457708</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761459707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 14 Columns, 252 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761459708</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Matte Tin, 0.254µm Gold	<u>1712981707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Left Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, MAPS, Lead Free	<u>1712981717</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 14 Columns, 252 Circuits,	<u>1712981725</u>

Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Matte Tin, 0.254µm Gold	
Impact 100 Ohm 6 Pair Vertical Backplane Header Left Guide, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Matte Tin, 0.254µm Gold	<u>1712983707</u>
Impact 100 Ohm 6 Pair Vertical Backplane Header Right Guide, Open Endwall, 14 Columns, 252 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Matte Tin, 0.254µm Gold	<u>1712985707</u>

This document was generated on Sep 16, 2025

Obsolete