



Color: ■ silver-colored

Similar to illustration



Dimensions in mm

Features:

- Duplex LC optical connector
- Small Form-Factor Pluggable (SFP) industry-standard design
- Compliant with Fast ETHERNET standard
- Differential LVPECL inputs and outputs
- Power supply: 3.3 V
- TTL signal detect indicator
- Hot-pluggable capability

Technical data	
Optical fiber type	Single-mode

Connection data	
Connection technology: communication/fieldbus	1 x SFP; LC fiber-optic connector
Connection requirement (permissible cable length)	30000 m
Connection requirement (permissible cable type)	Single-mode fiber 9/125 µm; Wavelength: 1310 nm



Physical data		
Width		13.4 mm / 0.528 inches
Height		13.3 mm / 0.524 inches
Depth		56.6 mm / 2.228 inches


Mechanical data		
Weight		25.5 g
Color		silver-colored

Environmental requirements		
Ambient temperature (operation)		0 ... +60 °C
Ambient temperature (storage)		-20 ... +80 °C
Fire load		0 MJ

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		TW
GTIN		4045454635411
Customs tariff number		85176200000





Product classification		
UNSPSC		43201553
eCl@ss 10.0		19-17-01-30
eCl@ss 9.0		19-17-01-06
ETIM 9.0		EC000309
ETIM 8.0		EC000309
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Approvals / Certificates				
General approvals			Declarations of conformity and manufacturer's declarations	
				
Approval	Standard	Certificate Name	Approval	Standard
EAC	TP TC 020/2011	EAC CoC 03083	EU-Declaration of Confor-	-
GZO Almaty Standart			mity	-
KC	Article 58-2, Clause 3	MSIP-REM-W43-SFP852	WAGO GmbH & Co. KG	
National Radio Research Agency				



Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 852-201/107-030	

Documentation				
System Description		Bid Text		
Industrial Switches – General Product Information	pdf			
	1873.93 KB			
		852-201/107-030	19.02.2019	xml
				3.78 KB
				
		852-201/107-030	09.03.2018	doc
				26.50 KB
				
		ausschreiben.de		
		852-201/107-030		

CAD/CAE-Data	
CAE data	
EPLAN Data Portal 852-201/107-030	
WSCAD Universe 852-201/107-030	