

**GLASS PASSIVATED
UNIDIRECTIONAL AND BIDIRECTIONAL
TRANSIENT VOLTAGE SUPPRESSORS**

REVERSE VOLTAGE - **5.0 to 170** Volts
POWER DISSIPATION - **500** WATTS


FEATURES

- Glass passivated chip
- Low leakage
- Uni and Bidirectional unit
- Excellent clamping capability
- The plastic material has U/L recognition 94V-0
- Fast response time

MECHANICAL DATA

- Case : Molded Plastic
- Marking : Unidirectional - type number and cathode band Bidirectional - type number only
- Weight : 0.34 grams

DO-15



DO-15		
Dim.	Min.	Max.
A	25.4	-
B	5.80	7.60
C	0.71 $\varnothing$	0.86 $\varnothing$
D	2.60 $\varnothing$	3.60 $\varnothing$
All Dimensions in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

CHARACTERISTICS	SYMBOLS	VALUE	UNIT
PEAK POWER DISSIPATION AT TA = 25°C, TP = 1ms (Note 1)	PPK	500	W
Peak Forward Surge Current 8.3ms single half sine-wave @ TJ = 25°C, (Note 2)	IFSM	70	A
Steady State Power Dissipation at TL = 120°C lead lengths 0.375" (9.5mm) , see fig. 4	PM(AV)	2.0	W
Maximum Instantaneous forward voltage at 16A for unidirectional devices only (Note 3)	VF	2.5	V
Operating Temperature Range	TJ	-55 to +175	°C
Storage Temperature Range	TSTG	-55 to +175	°C

NOTES : 1. Non-repetitive current pulse, per fig. 5 and derated above TA= 25°C per fig. 1
2. Uni-directional units only.
3. VF max=2.5V at IF=16 A 300us square wave pulse.

REV. 8, Nov-2014, KDID01

FIG.1 - PULSE DERATING CURVE




FIG.2 - TYPICAL JUNCTION CAPACITANCE




FIG.3 - PULSE RATING CURVE




FIG.4 - STEADY STATE POWER DERATING CURVE





FIG.5 - PULSE WAVEFORM



Type Number	Type Number	Reverse Standoff Voltage	Breakdown Voltage BV Volts @It			Max. Clamping Voltage @Ipp	Max. Peak Pulse Current	Max. Reverse Leakage @VR
(UNI)	(BI)	V _R (V)	Min (V)	Max (V)	It (mA)	V _c (V)	I _{pp} (A)	I _R (uA)
SA5.0A	SA5.0CA	5.0	6.40	7.07	10	9.2	54.3	600
SA6.0A	SA6.0CA	6.0	6.67	7.37	10	10.3	48.5	600
SA6.5A	SA6.5CA	6.5	7.22	7.98	10	11.2	44.6	400
SA7.0A	SA7.0CA	7.0	7.78	8.60	10	12.0	41.7	150
SA7.5A	SA7.5CA	7.5	8.33	9.21	1	12.9	38.8	50
SA8.0A	SA8.0CA	8.0	8.89	9.83	1	13.6	36.8	25
SA8.5A	SA8.5CA	8.5	9.44	10.43	1	14.4	34.7	10
SA9.0A	SA9.0CA	9.0	10.0	11.1	1	15.4	32.5	5
SA10A	SA10CA	10	11.1	12.3	1	17.0	29.4	3
SA11A	SA11CA	11	12.2	13.5	1	18.2	27.5	3
SA12A	SA12CA	12	13.3	14.7	1	19.9	25.1	3
SA13A	SA13CA	13	14.4	15.9	1	21.5	23.3	3
SA14A	SA14CA	14	15.6	17.2	1	23.2	21.6	3
SA15A	SA15CA	15	16.7	18.5	1	24.4	20.5	3
SA16A	SA16CA	16	17.8	19.7	1	26.0	19.2	3
SA17A	SA17CA	17	18.9	20.9	1	27.6	18.1	3
SA18A	SA18CA	18	20.0	22.1	1	29.2	17.1	3
SA20A	SA20CA	20	22.2	24.5	1	32.4	15.4	3
SA22A	SA22CA	22	24.4	27.0	1	35.5	14.1	3
SA24A	SA24CA	24	26.7	29.5	1	38.9	12.9	3
SA26A	SA26CA	26	28.9	31.9	1	42.1	11.9	3
SA28A	SA28CA	28	31.1	34.4	1	45.4	11.0	3
SA30A	SA30CA	30	33.3	36.8	1	48.4	10.3	3
SA33A	SA33CA	33	36.7	40.6	1	53.3	9.4	3
SA36A	SA36CA	36	40.0	44.2	1	58.1	8.6	3
SA40A	SA40CA	40	44.4	49.1	1	64.5	7.8	3
SA43A	SA43CA	43	47.8	52.8	1	69.4	7.2	3
SA45A	SA45CA	45	50.0	55.3	1	72.7	6.9	3
SA48A	SA48CA	48	53.3	58.9	1	77.4	6.5	3
SA51A	SA51CA	51	56.7	62.7	1	82.4	6.1	3
SA54A	SA54CA	54	60.0	66.3	1	87.1	5.7	3
SA58A	SA58CA	58	64.4	71.2	1	93.6	5.3	3
SA60A	SA60CA	60	66.7	73.7	1	96.8	5.2	3
SA64A	SA64CA	64	71.1	78.6	1	103.0	4.9	3
SA70A	SA70CA	70	77.8	86.0	1	113.0	4.4	3
SA75A	SA75CA	75	83.3	92.1	1	121.0	4.1	3
SA78A	SA78CA	78	86.7	95.8	1	126.0	4.0	3
SA85A	SA85CA	85	94.4	104.3	1	137.0	3.6	3
SA90A	SA90CA	90	100	110.5	1	146.0	3.4	3
SA100A	SA100CA	100	111	122.7	1	162.0	3.1	3
SA110A	SA110CA	110	122	134.8	1	177.0	2.8	3
SA120A	SA120CA	120	133	147.0	1	193.0	2.6	3
SA130A	SA130CA	130	144	159.2	1	209.0	2.4	3
SA150A	SA150CA	150	167	184.6	1	243.0	2.1	3
SA160A	SA160CA	160	178	196.7	1	259.0	1.9	3
SA170A	SA170CA	170	189	208.9	1	275.0	1.8	3

NOTE :

Suffix 'A' denotes 5% tolerance device.

1. Add suffix 'C' or 'CA' after part number to specify Bi-directional devices.
2. The IR limit is double for Bi-Directional devices.

Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.