





C-170002

1/16" : 1L DIMENSIONS IN MM, DO NOT SCALE PRINT

PRINT DIST



SECT. A-A



SECT. B-B

NOTE

- △ THESE ITEMS ARE FOR USE OTHER THAN IN JAPAN.
- △ GENERAL TOLERANCES; ± 0.4
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注記

- △ 海外向け製品。
- △ 一般公差; ± 0.4

△ OBSOLETE	1700022	17.0	8.7	4.0	7000	108-5003	BRASS	PRE-TIN
OBSOLETE	31700024	17.0	8.7	4.0	15000	108-5003	PHOS-BZ	POST-TIN
OBSOLETE	3-1	17.0	8.7	4.0	15000	-5003		
OBSOLETE	3-2	15.8	7.3	3.5	15000	-5004		POST-TIN
OBSOLETE	3-1	15.8	7.3	3.5	15000	-5004	PHOS-BZ	
OBSOLETE	2-5	17.0	8.7	4.0	20000	-5003	BRASS	
△	1-7	15.8	7.3	3.5	25000	-5004		
OBSOLETE	1-6	17.0	8.7	4.0	25000	-5003		
OBSOLETE	1-5	17.0	8.7	4.0	25000	-5003		
OBSOLETE	1-4	17.0	8.7	4.0	20000	-5003		POST-TIN
△	1-2	15.8	7.3	3.5	20000	-5004		POST-TIN
	1-1	15.8	7.3	3.5	20000	-5004		
	7	17.0	8.7	4.0	7000	-5004		
	5	17.0	8.7	4.0	5000	-5003		
	4	17.0	8.7	4.0	7000	-5003		POST-TIN
	1700022	17.0	8.7	4.0	7000	108-5004	BRASS	POST-TIN

PART NO.	LOOSE PCS NO	L1 DIM	L2 DIM	D DIM	QTY/REEL	PROD SPEC NO.	MATERIAL	FINISH
TE Connectivity								
WIRE RANGE		INSULATION DIA.		WIRE (NAME)				
25-227AWG (14-14)		2.5-3.8 mm		SHUR PLUG				
MATERIAL		FINISH		SPEC				
SEE TABLE		SEE TABLE		C J C-170002				
DR		CE		REV. R3				
CHK		APP		SHEET 1-1				

R3	REVISED PER ECR-19-012286	PC	TD	20SEP19
R2	REVISED PER ECO-11-005030	RK	HMR	22MAR11
LTR	REVISION RECORD	DR	CHK	DATE

(CUSTOMER DRAWING) 参考図面