



**Part Number :** [2202011071](#)

**Product Description :** 2.00mm Pitch, Micro-Lock Plus PCB Header, Dual Row, Vertical, Surface Mount, Matte Tin Plating, 10 Circuits, Low-Halogen, Black

**Series Number :** 220201

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[2202011071\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[2202011071.dxf](#)

### Specifications


[2202019200-SPK-200.pdf](#)

[2202000000-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)6375-DC (05 Nov 2025)  |
| EU RoHS            | Compliant per EU 2015/863   |

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | PCB Headers and Receptacles   |
| Series         | 220201  |
| Description    | 2.00mm Pitch, Micro-Lock Plus PCB Header, Dual Row, Vertical, Surface Mount, Matte Tin Plating, 10 Circuits, Low-Halogen, Black |
| Application    | Signal, Wire-to-Board   |
| Component Type | PCB Header  |
| Product Name   | Micro-Lock Plus   |
| UPC            | 196823499098  |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 2.8A             |
| Voltage - Maximum             | 250V AC (RMS)/DC |

### Physical

|           |    |
|-----------|----|
| Breakaway | No |
|-----------|----|

|                                |                       |
|--------------------------------|-----------------------|
| Circuits (Loaded)              | 10                    |
| Circuits (maximum)             | 10                    |
| Color - Resin                  | Black                 |
| Durability (mating cycles max) | 30                    |
| First Mate / Last Break        | No                    |
| Flammability                   | 94V-0                 |
| Glow-Wire Capable              | No                    |
| Guide to Mating Part           | No                    |
| Keying to Mating Part          | Yes                   |
| Lock to Mating Part            | Yes                   |
| Material - Metal               | Brass                 |
| Material - Plating Mating      | Matte Tin             |
| Material - Plating Termination | Matte Tin             |
| Material - Resin               | Polyamide             |
| Net Weight                     | 1716.850/mg           |
| Number of Rows                 | 2                     |
| Orientation                    | Vertical              |
| Packaging Type                 | Embossed Tape on Reel |
| PCB Locator                    | No                    |
| PCB Retention                  | Yes                   |
| Pitch - Mating Interface       | 2.00mm                |
| Pitch - Termination Interface  | 2.00mm                |
| Plating min - Mating           | 1.000µm               |
| Plating min - Termination      | 1.000µm               |
| Polarized to Mating Part       | Yes                   |
| Polarized to PCB               | Yes                   |
| Robotic Placement              | Vacuum Pick-Up Area   |
| Shrouded                       | Fully                 |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40° to +105°C        |
| Termination Interface Style    | Surface Mount         |

---

## Mates With / Use With

### Mates with Part(s)

| Description  | Part Number   |
|--|---------------|
| 2.00mm Pitch Micro-Lock Plus<br>Dual Row Receptacle Housings | <u>220200</u> |

---

This document was generated on Feb 05, 2026