



Fair-Rite Products Corp.

Your Signal Solution®



38M1020AA1212(000000000000)



Part Number: 38M1020AA1212

Material Grade	M1
Sheet Size	120 x 120 mm
Ferrite Thickness	0.2 mm
Total Thickness	0.23 mm



Weight: (g)

Chart Legend

Dim	mm	mm tol	nominal inch	inch misc.
A				

		Typical Shielding Effectiveness (dB): Test Method as noted -> **, ***				
PARTNUMBER	Material	1MHz**	6.78MHz**	13.56MHz**	100MHz***	300MHz***
38M1020AA1212	M1	3.6	3.6	3.6	4	3.3

** Shielding Effectiveness (SE) at 1 -50MHz :
measured using IEC 6233-2 Rde Inter Decoupling Ratio method (loop to loop distance= 6mm).

This method is meaningful as a measure of decoupling effectiveness circuit to circuit or to metal surfaces (plane to plane).

<p>*** Shielding Effectiveness (SE) at 100MHz+ : measured using IEC 6233-2 Rrs Radiation Suppression Ratio method (50-ohm Microstripline).</p>	
<p>This method is meaningful as a measure of shielding for radiated emissions of "antennas".</p>	

Equipment Used:

E5072A Vector Network Analyzer (30kHz - 8.5 GHz)
HP4291A RF Impedance/Material Analyzer (1MHz-3GHz)
E4991A with 16453A Dielectric Test Fixture
HP4284A for Temperature testing
25mm diameter slotted loop antennas
50-ohm Micro-Stripline Test Fixture



Fair-Rite Products Corp.

•

One Commercial Row, Wallkill, New York 12589-0288

888-324-7748

•

845-895-2055

•

Fax: 845-895-2629

•

ferrites@fair-rite.com

•

www.fair-rite.com