



© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B6	REVISED PER ECR-25-243298	07MAY2025	MK	MS











SECTION A–A

NOTES:

1. MATERIAL : PHOSPHOR BRONZE, THICKNESS : 0.20mm
2. FINISH : SEE TABLE
3. ACCEPTS HOUSING : 1735447, 2041423
4. APPLICABLE WIRES : AWG #30~#24
5. INSULATION O.D. : 0.9 TO 1.5mm
6. ADDED CHECK POINTS(P1,P2,P3) TO MEASURE PLATING THICKNESS AFTER STAMPING



SECTION B–B



SECTION C–C

PART NO.	FINISH
1735801-1	80μ" MIN. PRE-TIN PLATED OVER 50u'' MIN. NICKEL PLATED
1735801-2	100μ" MIN. PRE-MATTE TIN PLATED OVER 50μ" MIN. NICKEL PLATED
1735801-3	1μ" to 3μ" Gold plating on contact area, 1.27um min Nickel under-plate overall

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.3
2 PLC	± 0.3
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL 1 | FINISH 2

DWN	YMLEE	28APR2009
CHK	VTAN	18MAR2011
APVD	SFEONG	18MAR2011
PRODUCT SPEC	108-51087	
APPLICATION SPEC	114-57011	
WEIGHT	0	

TE Connectivity

NAME: 2.0MM PITCH HPI CRIMP CONTACT – –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1735801	—

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV B6

Downloaded from Arrow.com.