



E2E-X5B1T18-M1TJ 0.3M

Proximity sensor, inductive, nickel-brass, short body, M18, shielded, 8 mm, DC, 3-wire, PNP NO, IO-Link COM3, M12 pigtail
Smartclick connector, 0.3 m

Specifications

Size	M18
Mounting type	Flush
Sensing distance	5 mm
Overall length of sensor	55.3 mm
Thread length	34 mm
Material housing	Brass, nickel plated
Output type	IO-Link, PNP
Operation mode	NO
Connection method	M12 pigtail Smartclick connector
Cable specifications	PVC (oil-resistant)
Cable length	0.3 m
IO-Link function	✓
IO-Link baud rate	COM3 (230.4 kbps)
Degree of protection (IP)	IP67/IP67G/IP69K

Accessories



Y92E-J18S30

Mounting Sleeves e-jig for M18 Prox

Related products



M12 Connectors & Cordsets

Industrial connectors & cordsets for any application

Downloads

CAD Library



E2E NEXT Datasheet

EN PDF 39 MB



E2E(Q) - Basic Models Index list

EN PDF 719 KB



E2E(Q) - Premium Models Index list

EN PDF 719 KB



E2E[Q]-XxBxxxx IO-Link IODD file

EN ZIP 1.35 MB



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



IO-Link Series Brochure

EN PDF 6.25 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 11 October, 2025. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](https://www.industrial.omron.eu)