















PRODUCT NUMBER SEE SHEET 2



| | | | | | | | | | | | | | | | | | | | | | | | |
|---------------|--|---|--|--------|--|----------------|--|-------------|--|---|--|---|--|----------------|--|-----------|--|------------------|--|-----|--|---|--|
| spec ref | | * | | dr | | Vicking Liu | | 2015/12/02 | | projection | |  | | size | | A3 | | scale | | 3:2 | | | |
| tolerance std | | TOLERANCES UNLESS OTHERWISE SPECIFIED | | eng | | Vicking Liu | | 2015/12/25 | |  | |  | | ecn no | | - | | | | | | | |
| ASME Y14.5 | | | | chr | | Fancy Zhang | | 2015/12/25 | | | | | | rel level | | Released | | | | | | | |
| | | | | appr | | Pei-Ming Zheng | | 2015/12/25 | | | | | | product family | | PwrBlade+ | | | | | | | |
| surface | |  | | linear | | 0.X | | ±0.5 | |  | | title | | 24S + 13HDP | | dwg no | | 10106134-D006003 | | rev | | A | |
| | | | | 0.XX | | ±0.25 | | | | | | | | | | | | | | | | | |
| | | | | 0.XXX | | ±0.10 | | | | | | | | | | | | | | | | | |
| ASME Y14.5 | | angular | | 0° | | ±2° | | www.fci.com | | cat. no. | | Product - Customer Drw | | sheet 1 of 3 | | | | | | | | | |

| PRODUCT NO. | ROWS | | HIGH POWER | | | | | | | | | | | | | | SIGNAL | | | | | | | |
|--------------------|------------------|--|---|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|---|---|---|---|---|----|---|---|
| | | E1 | P13 | P12 | P11 | P10 | P9 | P8 | P7 | P6 | P5 | P4 | P3 | P2 | P1 | 6 | 5 | 4 | 3 | 2 | 1 | E2 | | |
| 10106134-D006003LF | D C B A |   |  | H3 | X | H3 | X | H3 | X | H3 | X | H3 | X | H3 | X | H1 |  | H | H | H | H | H | H |  |
| | | | | | | | | | | | | | | | | | G | G | G | G | G | G | | |
| | | | | | | | | | | | | | | | | | F | F | F | F | F | F | | |
| | | | | | | | | | | | | | | | | | E | E | E | E | E | E | | |
| | | | | | | | | | | | | | | | | | | | | | | | | |




| CODE | DESCRIPTION |
|------|-------------------------------|
| E | STD SIGNAL CONTACT, ROW A |
| F | STD SIGNAL CONTACT, ROW B |
| G | STD SIGNAL CONTACT, ROW C |
| H | STD SIGNAL CONTACT, ROW D |
| H1 | MFBL HIGH POWER CONTACT(3.43) |
| H3 | STD HIGH POWER CONTACT(3.43) |
| HA | METAL HOLD DOWN |
| X | OMITTED |



| | | | | | | | | |
|------------------------|----------------|----------------------------------|-----------------------------------|---------------------------|------------------|----------|--------------|-----|
| dr | Vicking Liu | 2015/12/02 | <div>projection</div> <div></div> | <div>MM</div> <div></div> | size | A3 | scale | 3:2 |
| eng | Vicking Liu | 2015/12/25 | | | ecn no | - | | |
| chr | Fancy Zhang | 2015/12/25 | | | rel level | Released | | |
| appr | Pei-Ming Zheng | 2015/12/25 | product family | PwrBlade+ | | | | |
| <div>www.fci.com</div> | | cat. no. | | Product - Customer Drw | | | sheet 2 of 3 | |
| <div>FCi</div> | | title | | | dwg no | | rev | |
| | | 24S + 13HDP RA STB RECEPTACLE | | | 10106134-D006003 | | A | |

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION: 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS ARE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION: GS-12-658.
APPLICATION SPECIFICATION: GS-20-141.
PRODUCT PACKAGED IN TRAYS: GS-14-1502.
- 9) THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL
MODULES AND END MODULES ARE OPTIONAL AND THE SHAPE
MAY BE DIFFERENT FOR OPTIMIZING THE MOLDING PROCESS. THE
VOID CORING WILL NOT EFFECT TO PRODUCT FUNCTION.

| | | | | | | | | | |
|--|----------------|------------|--|--|-----------|-------------------|-------|------------------|----------|
| dr | Vicking Liu | 2015/12/02 | <div>projection</div> <div></div> | <div>MM</div> <div></div> | size | A3 | scale | 3:2 | |
| eng | Vicking Liu | 2015/12/25 | | | ecn no | | | | - |
| chr | Fancy Zhang | 2015/12/25 | | | rel level | | | | Released |
| appr | Pei-Ming Zheng | 2015/12/25 | product family | | | PwrBlade+ | | | |
| <div></div> | | | title | | | 24S + 13HDP | | dwg no | |
| www.fci.com | | | cat. no. | | | RA STB RECEPTACLE | | 10106134-D006003 | |
| | | | Product - Customer Drw | | | sheet 3 of 3 | | rev | |
| | | | | | | | | A | |



Copyright FCI.