

Product data sheet

Specifications



MGE Galaxy 3500 Parallel Maintenance Bypass, up to 3 units 10-15kVA 208V Floormount

G35TSBPAR10K15F

⚠ Discontinued - Service only

⚠ Discontinued on: Nov 22, 2021

⚠ To be end-of-service on: Dec 31, 2031

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
rated power in VA	45000 VA
Provided equipment	Installation guide

Physical

Height	148.6 cm
Width	35.6 cm
Depth	83.8 cm
Net weight	121.82 kg
Mounting support	Floor
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Network frequency	60 Hz
-------------------	-------

Conformance

Standards	CSA C22.2 No 107.1 UL 1778
Product certifications	CSA

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	0...45 °C
Storage Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage altitude	0...9144 m
------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	166.37 cm
Package 1 Width	110.49 cm
Package 1 Length	72.39 cm
Package 1 Weight	156.36 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
EU RoHS Directive	Under investigation