

**SURFACE MOUNT
SUPER FAST RECTIFIERS**

REVERSE VOLTAGE - **50 to 400** Volts
FORWARD CURRENT - **1.0** Ampere


FEATURES

- Glass passivated chip
- Super fast switching for high efficiency
- For surface mounted applications
- Low forward voltage drop and high current capability
- Low reverse leakage current

MECHANICAL DATA

- Case : Molded plastic
- Case Material: Molding compound, UL Flammability classification 94V-0, "Halogen-free".
- Polarity : Indicated by cathode band
- Weight : 0.003 ounces, 0.093 grams

SMB



SMB		
DIM.	MIN.	MAX.
A	4.06	4.57
B	3.30	3.94
C	1.96	2.21
D	0.15	0.31
E	5.21	5.59
F	0.05	0.20
G	2.01	2.50
H	0.76	1.52
All Dimensions in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

CHARACTERISTICS	SYMBOL	ES1AB	ES1BB	ES1CB	ES1DB	ES1GB	UNIT
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	150	200	400	V
Maximum RMS Voltage	V _{RMS}	35	70	105	140	280	V
Maximum DC Blocking Voltage	V _{DC}	50	100	150	200	400	V
Maximum Average Forward Rectified Current @T _L =110°C	I _(AV)	1.0					A
Peak Forward Surge Current 8.3ms single half sine-wave super imposed on rated load (JEDEC METHOD)	I _{FSM}	30					A
Maximum forward Voltage at 1.0A DC	V _F	0.92				1.25	V
Maximum DC Reverse Current @T _J =25 °C at Rated DC Blocking Voltage @T _J =125 °C	I _R	5.0 200					uA
Maximum Reverse Recovery Time (Note 1)	T _{RR}	25					ns
Typical Reverse Recovery Time	T _{RR}	20					ns
Typical Junction Capacitance (Note 2)	C _J	20					pF
Typical Thermal Resistance (Note 3)	R _{θ JL}	25					°C/W
Operating Temperature Range	T _J	-55 to + 150					°C
Storage Temperature Range	T _{STG}	-55 to + 150					°C

NOTES : 1.Reverse Recovery Test Conditions :I_F=0.5A,I_R=1.0A,I_{RR}=0.25A.
2.Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
3.Thermal Resistance junction to Lead.

REV.-5, Oct-2019, KSGB09

FIG.1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - TYPICAL FORWARD CHARACTERISTICS





FIG.4 - TYPICAL REVERSE CHARACTERISTICS



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.