


108961-000 Product Details



108961-000

TE Part Number: 108961-000

Active

Add to Part List

Splices - Closed Barrel

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Splice
- Sealed
- Splice Type = Butt
- Butt Splice Type = Standard
- Body Style = DuraSeal

View all Features | Find Similar Products

Live Product Chat

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples

NEW!

Documentation & Additional Information

Product Drawings:

- DuraSeal Crimp Splice Environment Resistant (PDF, English)

Catalog Pages/Data Sheets:

- Wire and Cable,Harnessing and Protection Products (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Splice
- Sealed = Yes
- Splice Type = Butt
- Body Style = DuraSeal
- Insulation = Yes
- Insulation Support = Insulation Support
- Insulation Diameter (mm [in]) = 6.50 [.256] Max.
- Material = Copper
- Finish = Tin
- Color = Yellow
- Connection Type = Crimp
- Comment = Heat-Shrinkable

Mechanical Attachment:

- Inside Diameter (mm [in]) = 3.50 [1.470]

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Body Related Features:

- Butt Splice Type = Standard
- Wire Range (mm [AWG]) = 3.00-6.00² [12-10]
- Wire Range (CMA) = 5,874 – 9,354
- Insulation Type = Pre-Insulated
- Insulation Sleeve Material = Heat-Shrinkable Nylon
- Heat Shrinkable Insulation Material = Nylon

Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Operating Temperature (Max.) (°C) = 125

Operation/Application:

- Application Type = Wire to wire splicing

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = Raychem

Provide Website Feedback | Need Help?