

A

B

C


D

E

F

G

H



Materials

Pin (outer sleeve) :	Brass, machined, CuZn38Pb2
Clip (contact 4 finger) :	Beryllium copper, heat treated or PHBZ
Plating (outer sleeve) :	Tin plated : 2μm/80μ"nickel, 5μm/200μ" Tin
Plating clip (contact):	2μm/80μ"nickel, full gold
Insulator body (black) :	Glass filled thermoplastic polyester UL94V-0

Electrical

Current rating :	3 Amps/contact max.
Contact resistance :	Max 4mΩ
Insulation resistance :	Min 10,000mΩ @ 500 V AC
Operating Voltage :	100 VRMS / 150 V AC

Mechanical

Operating temperature : Tin plated: -40°C to +105°C
Average insertion force
with steel pin of: 0.43mm/0.017" <250g
Average withdrawal force
with steel pin of: 0.43mm/0.017" >50g
Mechanical life : min.200

Packaging:	Tube
------------	------

Scale	1:1							Name
TOLERANCE						Drawn	11.02.11	Chappel
X.X	±0.40					Approved	11.30.11	Warner
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°					 		
			Modification	Date	Name			

Item No.	
----------	--

AR28-HZL/01-TT-R

Title	IC-Socke, 28 Pin, Machined Contact, 10μ" Gold Plating, Pitch: 2.54MM, Pin Length: 7.43MM
--------------	--

Drawing No.

rev00

Replace

Sheet

