

## Conductor marking collar - UCT-WMS 4,7 (12X5,5) - 0828571

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: slide-on, for terminal block width: 5.2 mm, cable diameter range: 2.5 ... 4.7 mm, lettering field size: 12 x 5.5 mm, Number of individual labels: 45

### Your advantages

- ✓ The UCT-WMS ... UniCard labeling range includes markers that can be threaded onto conductors
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the THERMOMARK CARD and the BLUEMARK LED
- ✓ The markers support multi-line labeling
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts

**RoHS**

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	6 pc
GTIN	 4 046356 519694
GTIN	4046356519694
Weight per Piece (excluding packing)	16.670 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Length (b)	12 mm
Width (a)	5.5 mm
Height (c)	7.1 mm
Cable diameter	2.5 mm ... 4.7 mm

# Conductor marking collar - UCT-WMS 4,7 (12X5,5) - 0828571

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

### General

Note	Can be labeled via thermal transfer
Color	white
Type	Card form
Components	free from silicone and halogen
Material	PC V0
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	45
Number of individual labels per row	9
Marking mounting type	slide-on
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3

### Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 9.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530

## Conductor marking collar - UCT-WMS 4,7 (12X5,5) - 0828571

### Classifications

#### ETIM

ETIM 6.0	EC001530
ETIM 7.0	EC001530

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

#### Magazine

Magazine - THERMOMARK CARD-UCT-MAG3 - 5146613



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-WMS...)

Magazine - P1 UC-MAG 7 - 5146568



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating: UC-WMCO...

## Conductor marking collar - UCT-WMS 4,7 (12X5,5) - 0828571

### Accessories

Magazine - TMP-UCT-MAG3 - 0803344



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMS...

---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>