

COAXIAL CONNECTOR, BNO, X Ohm, Straight cable jack (female)
21_BNO-0-4-1/133_N

Properties

- Used with balanced twin-conductor cables with 75 ohm to 130 ohm impedance
- Suitable for applications up to 200 MHz
- Ideal for computer networks and process control



Product configuration	
Gender	Standard
jack	IEC 60169-22

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Interface frequency	0.2 GHz

Mechanical data	
Weight	0.0161 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-50 °C ... 125°C

Ordering Information Table		
Item number	Item description	Packaging type
22541081	21_BNO-0-4-1/133_NE	Single

COAXIAL CONNECTOR, BNO, X Ohm, Straight cable jack (female)
21_BNO-0-4-1/133_N

Suitable cables	
Cable group	V1 - 2 mm / 78 Ohm
Suitable cables	RG_108_A/U
Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2913 / Date of publication: 25.11.2023 / uncontrolled copy