

Uzs

4.5mmL Chip Type



For SMD



Smaller

Anti-Solvent
Feature

- Chip type with 4.5mm height.
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).
- AEC-Q200 compliant. Please contact us for details.

UZT

High
Temperature

UWX

Smaller

Uzs

Smaller


UZR



■ Specifications


Item	Performance Characteristics							
Category Temperature Range	-40 to + 85°C							
Rated Voltage Range	4 to 50V							
Rated Capacitance Range	1 to 220μF							
Capacitance Tolerance	+20% at 120Hz, 20°C							
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01 CV or 3 (μA) ,whichever is greater.							
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C							
	Rated voltage (V)	4	6.3	10	16	25	35	50
	tan δ (MAX.)	0.50	0.30	0.24	0.19	0.16	0.14	0.14
Stability at Low Temperature	Measurement frequency : 120Hz							
	Rated voltage (V)	4	6.3	10	16	25	35	50
	Impedance ratio ZT / Z20 (MAX.)	Z-25°C / Z+20°C	7	4	3	2	2	2
		Z-40°C / Z+20°C	15	8	8	4	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.							
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.							
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.							
Marking	Black print on the case top.							

■ Chip Type



※ Voltage mark for 6.3V is 「6V」.

Type numbering system (Example : 16V 10μF)



● Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

● Dimension table in next page.

UZZ

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μF)	Case Size φD×L (mm)	tan δ	Leakage Current (μA) (at 20°C after 2 minutes)	Rated Ripple (mArms) (85°C/120Hz)	Part Number
4 (0G)	33	4×4.5	0.50	3	28	UZZ0G330MCL1GB
	47	4×4.5	0.50	3	33	UZZ0G470MCL1GB
	100	5×4.5	0.50	4	56	UZZ0G101MCL1GB
	220	6.3×4.5	0.50	8.8	96	UZZ0G221MCL1GB
6.3 (0J)	22	4×4.5	0.30	3	28	UZZ0J220MCL1GB
	33	5×4.5	0.30	3	37	UZZ0J330MCL1GB
	47	5×4.5	0.30	3	45	UZZ0J470MCL1GB
	100	6.3×4.5	0.30	6.3	70	UZZ0J101MCL1GB
10 (1A)	22	5×4.5	0.24	3	33	UZZ1A220MCL1GB
	33	5×4.5	0.24	3.3	41	UZZ1A330MCL1GB
	47	6.3×4.5	0.24	4.7	52	UZZ1A470MCL1GB
16 (1C)	10	4×4.5	0.19	3	23	UZZ1C100MCL1GB
	22	5×4.5	0.19	3.52	37	UZZ1C220MCL1GB
	33	6.3×4.5	0.19	5.28	49	UZZ1C330MCL1GB
	47	6.3×4.5	0.19	7.52	58	UZZ1C470MCL1GB
25 (1E)	4.7	4×4.5	0.16	3	16	UZZ1E4R7MCL1GB
	10	5×4.5	0.16	3	27	UZZ1E100MCL1GB
	22	6.3×4.5	0.16	5.5	42	UZZ1E220MCL1GB
	33	6.3×4.5	0.16	8.25	52	UZZ1E330MCL1GB
35 (1V)	4.7	4×4.5	0.14	3	18	UZZ1V4R7MCL1GB
	10	5×4.5	0.14	3.5	29	UZZ1V100MCL1GB
	22	6.3×4.5	0.14	7.7	46	UZZ1V220MCL1GB
50 (1H)	1	4×4.5	0.14	3	8.4	UZZ1H010MCL1GB
	2.2	4×4.5	0.14	3	13	UZZ1H2R2MCL1GB
	3.3	4×4.5	0.14	3	17	UZZ1H3R3MCL1GB
	4.7	5×4.5	0.14	3	20	UZZ1H4R7MCL1GB
	10	6.3×4.5	0.14	5	33	UZZ1H100MCL1GB

- Taping specifications are given in page 20.
- Recommended land size, soldering by reflow are given in page 16, 17.
- Please select UUR(p.171), UUG(p.181) if high C/V products are required.
- Please refer to page 3 for the minimum order quantity.