


0263.750 - 263 Series



Series: 263

Fuse 263 Datasheet

The PICO® II 263 Series Fuse is a specially designed axial leaded fuse that achieves a 250V rating in a small package.

Features:

- Very fast-acting
- Small size
- Wide current rating range (62mA- 15A)
- RoHS compliant
- Halogen-free available
- Wide operating temperature range
- Low temperature rerating
- 250V rating

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

NEW! Product Selection Guide eCatalog
[Read Now](#)

Electronics
News and Information

Feedback

Electrical Characteristics		Technical Resources	Environmental Info
Property (Mouseover for details)	Value		
Ampere Rating (A)	0.75		
Body	Glass Body		
Nominal Melting I²T (A²sec)	0.0411		
Interrupting Rating	50A@250VAC		
Moisture Sensitivity Level	MIL-STD-202 Method 106.		
Min Operating Temp °C	-55		
Max Operating Temp (°C)	125		
Nominal Voltage Drop (mV)	0.176		
Nominal Cold Resistance (Ohms)	0.15		
Opening	Very Fast-Acting (FF)		
Package Size	3.68 x 7.62mm		
VAC (V)	250		

Connect with Littelfuse
Sign up to receive special offers and news
 [Submit](#)

For more details about how we use your information, check our [Privacy Statement](#).

Mobile Site

About Littelfuse

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

Explore Littelfuse

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

Technical Resources

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents