

Full Motion Dual Desk Clamp for 13" to 27" Monitors and Laptops Up to 15"

MODEL NUMBER: DDR1327NBMSC



Mounts a monitor and a laptop off the surface of your desk, table or workstation to free up valuable space. Ideal for home or office use.

Description

The VESA-compliant DDR1327NBMSC Full Motion Dual Desk Clamp attaches to your desk, table or workstation, allowing you to mount a monitor and a laptop above it and free up valuable workspace. Ideal for home and office, the DDR1327NBMSC fits most flat-panel displays from 13 to 27 inches and laptops up to 15 inches.

Dual swivel arms can be independently adjusted for angle and height to give you maximum flexibility in positioning your displays to fit your environment and comfort level. Move a screen closer to you, or push both screens out of your way when not in use. The monitor mount's 180° swivel and -80° to 90° tilt capability minimizes glare and provides comfortable viewing from multiple angles. The laptop mount swivels 180° with a 25° tilt capability. The monitor mount rotates 360° for viewing in portrait or landscape orientation.

Durable clamp attaches to most flat surfaces up to 2.4 inches thick for a firm grip. The unit supports monitors up to 22 lbs (9.9 kgs) and laptops up to 11 lbs (4.9 kgs). The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Attaches to Most Desks, Tables and Workstations

- Clamps securely to most flat surfaces from 0.4 in. to 2.4 in.
- Fits most flat-panel displays from 13 to 27 in.
- Fits most laptops up to 15 in.

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- Fits most laptops up to 15 in.
- One-touch adjustment for comfortable viewing
- Supports monitors up to 22 lbs (9.9 kgs) and laptops up to 11 lbs (4.9 kgs)

Package Includes

- Desk mount assembly
- End cap
- (2) Arms
- Notebook holder
- Notebook mounting assembly
- Monitor mounting assembly
- (3) Collars
- (2) Sleeves
- (2) Knobs
- (2) Front safety clips
- (2) Side safety clips
- (4) M4 screws
- (4) M5 screws
- (4) Washers
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Dual swivel arms adjust independently for angle and height
- Ideal for home and office use

Convenient One-Touch Adjustment

- Monitor mount swivels 180° with -80° to 90° tilt capability for comfortable viewing from multiple angles
- Laptop mount swivels 180° with 25° tilt capability
- Monitor mount rotates 360° for viewing in portrait or landscape orientation

Durable Metal Construction

- Monitor arm supports up to 22 lbs (9.9 kgs)
- Laptop arm supports up to 11 lbs (4.9 kgs)
- Scratch-resistant powder-coated finish blends with any décor
- Mounting hardware included

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

Specifications

OVERVIEW	
UPC Code	037332186225
Device Compatibility	Monitor/HDTV
PHYSICAL	
Material of Construction	Steel
Color	Black; Silver
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	-80/+90 Tilt; 180 Swivel; 360 Rotate
Laptop Display Size (cm)	12.7 - 38.1
Laptop Display Size (in.)	5 - 15
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	22
Maximum Weight Capacity (kg)	10



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Number of Displays	2
Shipping Dimensions (hwd / cm)	12.50 x 51.79 x 24.79
Shipping Dimensions (hwd / in.)	4.92 x 20.39 x 9.76
Shipping Weight (kg)	4.38
Shipping Weight (lbs.)	9.65
Unit Dimensions (hwd / in.)	12.52 x 33.86 x 4.45
Unit Dimensions (hwd / cm)	31.80 x 86.0 x 11.30
Unit Weight (lbs.)	7.53
Unit Weight (kg)	3.42
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>