




| REVISION RECORD |     |             |      |      |
|-----------------|-----|-------------|------|------|
| REV             | ECO | DESCRIPTION | DRFT | CHKD |
|                 |     |             |      |      |



P.C.B. Layout (TOP VIEW) t=1

NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : NYLON FR52(HIGH TEMPERATURE)
2. CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
3. PLATING : 1: CONTACT AREA- SELECTIVE GOLD PLATING.  
2: TAILS- 150u" TIN-LEAD MIN OVER 50u" NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: 0°C TO 70°C.
3. REFLOW SOLDERING TEMPERTUR: 255°C TO 265°C 5-10SECOND.

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68, SUBPART F.

ROHS PART NUMBER: E666X-1X026X-L

2C-2 1-3u" 2-6u"  
4C-4 3-15u" 4-30u"  
6C-6 1-TIN 5-50u"  
2-NICKEL

|                |                                                                                       |  |                |                         |                                |              |     |
|----------------|---------------------------------------------------------------------------------------|--|----------------|-------------------------|--------------------------------|--------------|-----|
| DETACHED LISTS | <div>MM<br/>(INCH)</div>                                                              |  | DFTO SAMMY     | DATE 04/11/05           | FULL RISE ELECTRONIC CO., LTD  |              |     |
|                | TOLERANCES EXCEPT AS NOTED                                                            |  | CHKDQIANPU     | DATE2005/4/11           |                                |              |     |
|                | MM                                                                                    |  | MFO            | DATE                    | TITLE                          |              |     |
|                | .0 ±0.20                                                                              |  | APPPVILLUSHENG | DATE2005/4/12           |                                |              |     |
|                | .00 ±0.15                                                                             |  | MATERIAL :     |                         | RJ11 SIDE ENTRY PCB JACK (SMD) |              |     |
|                | .000 ±0.075                                                                           |  | ANGLES ±       |                         |                                |              |     |
|                |  |  | QT*Y :         | DRAWING NO. GE663004-LA |                                | SIZE         | REV |
|                | THIRD ANGLE PROJECTION                                                                |  | FINISH :       | /PART NO. SEE NOTE      |                                | A3           | 0   |
|                |                                                                                       |  | SCALE :        | DO NOT SCALE DRAWING    |                                | SHEET X OF Y |     |
|                |                                                                                       |  |                |                         |                                |              |     |