


2-1734858-3 Product Details

 Share

 Print

 Email



2-1734858-3

TE Internal Number: 2-1734858-3

 Active

 View 3D PDF

PCB Mounted Jacks - Single Port, Multi-port and Stacked

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Preloaded
- Single Port Configuration
- 1 x 1 Jack Configuration
- Jack Type = RJ45

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information	
Product Drawings: MODULAR JACK, RJ45/RJ11, TOP ENTRY, SMT TYPE (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version A) 3D Model (IGES, Version A) 3D Model (STEP, Version A)	Additional Information: Product Line Information Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Connector - Jack Type = RJ45 - PCB Mounting Orientation = Top Entry (Vertical) - PCB Mount Style = Surface Mount - Termination Method to PC Board = Solder - Performance Category = Cat 3 - LED = Without - Grounding Options = Without - Panel Stops = Without - Keyed = No - Profile = Standard - Color = Black Mechanical Attachment: - Panel Mount Retention = Without - Flanged = No Electrical Characteristics: - Shielded = No Termination Features: - Solder Tail Contact Plating = Gold Flash over Nickel Dimensions: - Height (mm [in]) = 15.90 [0.626] - PCB Thickness, Recommended (mm [in]) = 1.57 [0.062] Body Features: - Inverted Jack Face = No	Contact Features: - Contact Plating, Mating Area, Material = Gold (30) - Contact Base Material = Phosphor Bronze Housing Features: - Housing Material = High Temperature Thermoplastic - UL Flammability Rating = UL 94V-0 Configuration Features: - Preloaded = Yes - Port Configuration = Single - Jack Configuration = 1 x 1 - Number of Positions = 8 - Number of Contacts Loaded = 8 Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C - RoHS/ELV Compliance History = Always was RoHS compliant Packaging Features: - Packaging Method = Reel - Packaging Quantity = 350 Product Availability: - Region = Asia, North America Other: - Brand = TE Connectivity

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed



© 2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | [Provide Website Feedback](#)

Downloaded from [Arrow.com](#)