

Straddle SMT type female connector for PCB


HDRA-E68FT2-()+

For PCB

Straddle SMT

ANSI/SFF8441


RoHS



● Configuration of product Part No.

HDRA- E 68 FT 2- () +

- ① Series name
② No. of contacts: 68
③ Type of contact
FT: Straddle SMT type, female
④ PCB thickness: 0.5 mm
⑤ Lock screws
Blank: None
SL : provided



● Components

①	Contacts
②	Insulator A
③	Insulator B
④	Square nuts
⑤	Lock screws
⑥	Shell

Mating connector: HDRA series IDC type male cable connector, or straddle SMT type male connector